

# MCM AUDIO SELECT™

## Sealed Back - Poly Treated Cone Midrange

### 5" Sealed Back Midrange

Ideal for any three way speaker system in home , automotive or prosound applications. Sealed back design ensures consistent performance regardless of mounting arrangement, and greatly eases cabinet design and construction when incorporating into your own designs.

#### Features

- Broad frequency range
- Poly treated paper cone
- Foam surround
- Fully enclosed stamped steel frame
- 13.3 oz. magnet
- 1" voice coil
- 


#### Specifications:

- Power capacity: 50W/70W RMS/peak
- Nominal impedance: 8Ω
- Frequency response: 500Hz ~ 10KHz
- Sensitivity: 94dB (W/M)
- 

#### Dimensions:

- Overall frame diameter: 5.18"
- Required cutout: 4.33"
- Mounting depth: 2.17"

### Response Curve:



Dimensions (mm):

