


Number of contacts

Mounting height

Standard Versions

9-37  
50



Turned solder pins, angled with/without snap-in-clips and grounding board locks

Identification	No. of contacts	Part No.	
<b>Performance levels</b> Explanations see page 05.04 Other performance levels on request		Performance level 3	Performance level 2
<b>Male connector</b> metal shell with dimples		2.84 mm pitch	2.84 mm pitch
With snap-in clips and grounding board locks	9 15 25 37 50	09 66 163 781 09 66 263 781 09 66 363 781 09 66 463 781 09 66 563 781	09 66 163 681 09 66 263 681 09 66 363 681 09 66 463 681 09 66 563 681
		2.54 mm pitch	2.54 mm pitch
	9 15 25 37 50	09 66 162 781 09 66 262 781 09 66 362 781 09 66 462 781 09 66 562 781	09 66 162 681 09 66 262 681 09 66 362 681 09 66 462 681 09 66 562 681
Without snap-in clips and grounding board locks	9 15 25 37 50	09 66 123 780 09 66 223 780 09 66 323 780 09 66 423 780 09 66 523 780	09 66 123 680 09 66 223 680 09 66 323 680 09 66 423 680 09 66 523 680
		2.54 mm pitch	2.54 mm pitch
	9 15 25 37 50	09 66 122 780 09 66 222 780 09 66 322 780 09 66 422 780 09 66 522 780	09 66 122 680 09 66 222 680 09 66 322 680 09 66 422 680 09 66 522 680
Please insert digit for flange thread or fitted female screw locks			
M3 ▶ 1 4-40 UNC ▶ 2 fitted screw locks 4-40 UNC ▶ 3			