


**THK.209.44**

TeeBox 7mm to 14mm cable max IP68 rated Screw fixing 4 cable entries 16A supplied complete with 4+4 connector (THB.032.A4B) enabling 4 wires/per pole (2 each side) making cabling easier and faster. Terminal block accepts up to 4mm Sq conductors and is rated at 32A 450V.



**PRODUCT SPECIFICATIONS**

|                             |                                    |
|-----------------------------|------------------------------------|
| Temperature "T" rating      | T85                                |
| Minimum cable diameter (mm) | 7                                  |
| Maximum cable diameter (mm) | 14                                 |
| Fixing system               | Screw                              |
| Comments                    | Photo is representative of product |
| Cable entries               | 4                                  |
| Body material               | PA66 / SEBS/ TPE                   |
| Max current (A)             | 16                                 |
| Minimum temp rating °C      | -40                                |
| Max temp rating °C          | 125                                |
| IP rating                   | 68                                 |