

Hose and Cable Protection Systems  
**FloorTrak® Floor Cable Cover**



**FloorTrak 2**

Color	Length Feet (meters)	Catalog Number
Black	10.0' (3.05)	<b>FT2BK10</b>
Brown	10.0' (3.05)	<b>FT2BR10</b>
Beige	10.0' (3.05)	<b>FT2BG10</b>
Gray	10.0' (3.05)	<b>FT2GY10</b>
Yellow	10.0' (3.05)	<b>FT2Y10</b>



**FloorTrak 4**

Color	Length Feet (meters)	Catalog Number
Black	5.0' (1.52)	<b>FT4BK5</b>
Black	25.0' (7.62)	<b>FT4BK25</b>
Gray	25.0' (7.62)	<b>FT4GY25</b>
Yellow	5.0' (1.52)	<b>FT4Y5</b>
Yellow	25.0' (7.62)	<b>FT4Y25</b>




**FloorTrak 3**

Color	Length Feet (meters)	Catalog Number
Black	5.0' (1.52)	<b>FT3BK5</b>
Black	25.0' (7.62)	<b>FT3BK25</b>
Brown	5.0' (1.52)	<b>FT3BR5</b>
Brown	25.0' (7.62)	<b>FT3BR25</b>
Beige	5.0' (1.52)	<b>FT3BG5</b>
Beige	25.0' (7.62)	<b>FT3BG25</b>
Gray	5.0' (1.52)	<b>FT3GY5</b>
Gray	25.0' (7.62)	<b>FT3GY25</b>
Yellow	5.0' (1.52)	<b>FT3Y5</b>
Yellow	25.0' (7.62)	<b>FT3Y25</b>



**FloorTrak 10 (Heavy Duty)**

Color	Length Feet (meters)	Catalog Number
Black	3.0' (.914)	<b>FT10BK3</b>
Black	5.0' (1.52)	<b>FT10BK5</b>
Yellow	3.0' (.914)	<b>FT10Y3</b>
Yellow	5.0' (1.52)	<b>FT10Y5</b>



**Dimensions**

FloorTrak	FT2 inches (mm)	FT3 inches (mm)	FT4 inches (mm)	FT10 (Heavy Duty) inches (mm)
Width (A)	2.75" (69.9)	3.00" (76.2)	3.25" (82.6)	5.6" (142.24)
Height (B)	.53" (13.5)	.75" (19.1)	1.10" (27.9)	1.7" (43.18)
Center Hole (CxD)	.60" x .31" (15.2) x (7.9)	.75" x .50" (19.1) x (12.7)	1.21" x .75" (30.7) x (19.1)	1.81" x 1.25" (45.98 x 31.75)

**Accessories**

Description	Catalog Number
1" Wide, 75' Roll Double-Sided Adhesive Tape.	<b>FTT1</b>
2" Wide, 75' Roll Double-Sided Adhesive Tape.	<b>FTT2</b>



**Specifications**

Material	Rigid PVC.
Operating Temperature	0°F to +120°F (-18°C to +49°C).