

H6,0/20D GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

| | |
|------------|---|
| Type | H6,0/20D GE |
| Order No. | 9019220000 |
| Version | Wire end ferrule, 6 mm ² , 12 mm, Colour code: DIN, Yellow (RAL 1023) |
| GTIN (EAN) | 4008190151607 |
| Qty. | 100 pc(s). |

Data sheet

H6,0/20D GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|--------|-------|------------|--------|
| Length | 20 mm | Net weight | 0.36 g |
|--------|-------|------------|--------|

Product data

| | | | |
|-------------------------------|-------------------|---|--------|
| Conductor cross-section | 6 mm ² | Wire connection cross section AWG, max. | AWG 10 |
| Contact surface length (L2) | 12 mm | Contact surface diameter (D1) | 3.5 mm |
| Collar diameter (D2) | 6.3 mm | Metal sleeve thickness (S1) | 0.2 mm |
| Plastic collar thickness (S2) | 0.3 mm | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000005 | UNSPSC | 31-16-31-02 |
| eClass 5.1 | 27-40-02-01 | eClass 6.2 | 27-40-02-01 |
| eClass 7.1 | 27-40-02-01 | | |

Approvals

Approvals



ROHS Conform