



with up to 4 cable entries

Identification	Size	Part number	Drawing	Dimensions in mm												
Split Hood for 3 cable entries for 4 cable entries Range of delivery: 2 split hood halves Cable entry glands order separately	16 B 24 B	09 30 016 0408 09 30 024 0408														
Housings bulkhead mounting 	16 B 24 B	09 30 016 0301 09 30 024 0301	<table border="1"> <thead> <tr> <th>Size</th> <th>a</th> <th>b</th> <th>Panel cut out</th> </tr> </thead> <tbody> <tr> <td>16 B</td> <td>103</td> <td>113</td> <td>82 x 35</td> </tr> <tr> <td>24 B</td> <td>130</td> <td>140</td> <td>108 x 35</td> </tr> </tbody> </table>	Size	a	b	Panel cut out	16 B	103	113	82 x 35	24 B	130	140	108 x 35	
Size	a	b	Panel cut out													
16 B	103	113	82 x 35													
24 B	130	140	108 x 35													
Identification	cable Ø	Part number	Drawing	Dimensions in mm												
Cable entry glands from Ø 10 mm upwards additional strain relief can be provided by cable ties (max. width 8 mm) for ASI cable	3 ... 4 4 ... 5 5 ... 6 6 ... 7 7 ... 8 8 ... 9 9 ... 10 10 ... 11 11 ... 12 12 ... 13 13 ... 14 14 ... 15 15 ... 16 -	09 00 000 5351 09 00 000 5352 09 00 000 5353 09 00 000 5354 09 00 000 5355 09 00 000 5356 09 00 000 5357 09 00 000 5358 09 00 000 5359 09 00 000 5360 09 00 000 5361 09 00 000 5362 09 00 000 5363 09 00 000 5364														
blind grommet	-	09 00 000 5350														
Identification strips order separately 20 pieces in one block 9 mm width / 20 mm length	-	09 33 000 9982														

Accessories