

Protect It! 8-Outlet Surge Protector, 6-ft. Cord, 2160 Joules, Tel/DSL Protection, Cord Clip

MODEL NUMBER: TLP806TEL



Highlights

- 8 outlets / 6-ft. cord
- 2160 joule rating
- Modem/fax surge protection
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

- Ideal for home computers and other important electrical equipment

Package Includes

- TLP806TEL
- 6-ft. telephone cord
- Instruction manual with warranty information

Description

Tripp Lite's TLP806TEL surge suppressor has 8 outlets, an 6-ft. cord with a space-saving right-angle plug, and diagnostic LEDs. The unit has a surge suppression rating of 2160 joules to handle the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Features

- 2160 joules AC surge suppression shields equipment from the strongest surges and line noise
- 8 AC outlets with room for 2 transformer plugs without blocking outlets covers computers and all peripherals
- Long 6 foot AC line cable with space-saving angle input plug conveniently reaches distant outlets
- Built-in RJ11 jacks (1in/1 out) prevent surges from damaging your modem/fax/phone equipment
- Built-in cord management
- Lighted power switch with integrated 15 amp circuit breaker offers power control and overload protection
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Attractive black suppressor housing with keyhole mounting tabs allow versatile placement options
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW	
Style	Strip
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) 5-15R



Output (Watts)	1800W
Circuit Breaker (amps)	15
Transformer Accommodation	Supports 2 large transformer plug accessories without covering remaining outlets, accepts up to 6 transformers total
Outlet Safety Covers	Includes built-in sliding outlet safety covers
Outlet Orientation	Single row of 6, plus 2 for transformer accommodation
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Plug Features	Space-saving right angle input plug
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	144000
LEDS ALARMS & SWITCHES	
Switches	Combination AC circuit breaker and 2-position red illuminated on/off power switch
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2160
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	330/400/400
EMI / RFI Filtering	Up to 40 dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	



Shipping Dimensions (hwd / in.)	13.78 x 5.13 x 2.40
Shipping Dimensions (hwd / cm)	35 x 13.03 x 6.1
Shipping Weight (lbs.)	1.5
Shipping Weight (kg)	.68
Unit Dimensions (hwd / in.)	1.74 x 2.00 x 12.40
Unit Dimensions (hwd / cm)	4.42 x 5.08 x 31.5
Unit Weight (lbs.)	1.2
Unit Weight (kg)	.54
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Keyhole mounting slots enable wall mounting
Receptacle Color	Black
Color (AC Line Cord)	Black
Color	Black
Outlets Measurement (Center to Center)	29mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between horizontal slots 101.3mm = Distance between vertical slots = 30mm
SPECIAL FEATURES	
Additional Information	Pair of phone line output jacks serve as a line splitter to enable the protection of two devices sharing a single dialup phone line
Right-Angle Plug	Yes
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Industry Canada (Communications)	Industry Canada
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 Ultimate Lifetime Insurance
---	---

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.