



RE932-04

- Epoxy fibre-glass FR4 1.50 mm
- Double-sided 35 µm Cu
- Plated through holes (PTH)
- Surface chem. Ni/Au with solder stop mask
- Adaption circuit board for SO 16
- Pitch: 1.27 mm (153 mil)
- Hole diameter 1.00 mm
- Size 13.65 x 20.32 mm

Module-No.	Pitch	mil	Pin	Size (mm)
RE932-04	1.270 mm	0.50	16	3.90 (153 mil)