



Dimensions Inches (mm)

Style	Stamped Steel							
	1-Gang Deep	2-Gang Deep	3-Gang Deep	1-Gang Shallow	2-Gang Shallow	3-Gang Shallow	1-Gang Deep	1-Gang Shallow
 Collar Material: Brass Aluminum	 B2431* BA2431*	 B2432 BA2432	 B2433 BA2433	 B2421* BA2421*	 B2422 BA2422	 B2423 BA2423	 B2427* -	 B2429* -
Min. Depth of Pour	3.75" (95.3)	3.75" (95.3)	3.75" (95.3)	2.75" (69.9)	2.75" (69.9)	2.75" (69.9)	4.00" (101.6)	3.00" (76.2)
Adjustability	Fully	Fully	Fully	Fully	Fully	Fully	Fully	Fully
Before Pour External Height Adjustment	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)
After Pour Internal Height Adjustment	.50" (12.7)	.50" (12.7)	.50" (12.7)	.50" (12.7)	.50" (12.7)	.50" (12.7)	.38" (9.5)	.38" (9.5)
Cubic Inch (cm3) Capacity Per Gang	60.0 cu. in. (983.2 cm3)	52.8 cu. in. (865.2 cm3)	50.8 cu. in. (832.5 cm3)	39.5 cu. in. (647.3 cm3)	35.0 cu. in. (573.5 cm3)	34.0 cu. in. (557.2 cm3)	54.0 cu. in. (884.9 cm3)	37.3 cu. in. (611.2 cm3)
Dimensions – A	3.72" (94.5)	3.72" (94.5)	3.72" (94.5)	2.74" (69.6)	2.74" (69.6)	2.74" (69.6)	3.90" (99.1)	2.81" (71.4)
Dimensions – B	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)	4.81" (122.2)
Dimensions – C	6.00" (152.4)	9.25" (235.0)	12.50" (317.5)	6.00" (152.4)	9.25" (235.0)	12.50" (317.5)	6.00" (152.4)	6.00" (152.4)
Dimensions – D	4.38" (111.3)	4.38" (111.3)	4.38" (111.3)	4.38" (111.3)	4.38" (111.3)	4.38" (111.3)	4.38" (111.2)	4.38" (111.2)
Dimensions – E	3.19" (81.0)	6.44" (163.6)	9.67" (245.6)	3.19" (81.0)	6.44" (163.6)	9.67" (245.6)	3.19" (81.0)	3.19" (81.0)
Knockouts – Sides	(1) ¾",1",1¼"	(2) ¾",1",1¼"	(3) ¾",1",1¼"	(2) ½",1) ¾"	(4) ½",1) ¾"	(6) ½",1) ¾"	(1) ½",1) 1¼"	(2) ½",1) ¾"
Knockouts – Ends	(1) ¾",1",1¼"	(1) ¾",1",1¼"	(1) ¾",1",1¼"	(1) ½",1) ¾"	(2) ½",1) ¾"	(2) ½",1) ¾"	(1) ¾",1) 1"	(1) ½",1) ¾"
Knockouts – Bottom	(2) ¾",1",1¼"	(4) ¾",1",1¼"	(6) ¾",1",1¼"	(2) ¾",1",1¼"	(4) ¾",1",1¼"	(6) ¾",1",1¼"	(3) ½",2) ¾"	(3) ½",2) ¾"
Concrete Cover Included	✓	✓	✓	✓	✓	✓	✓	✓
Closure Plugs Included	-	-	-	-	-	-	-	-
Removable LV Barrier	-	✓	✓	-	✓	✓	-	-

Note: UL File Number E92074.
 CSA File Number LR18416.
 *Suitable for single service applications only.

Carpet Flanges

Tapered Flange		1-Gang		2-Gang		3-Gang	
Number of Gangs	Dimensions	6.00" x 4.85"		6.00" x 8.13"		6.00" x 11.34"	
Brass	SB3083			SB3084			
Aluminum	SA3083			SA3084			
Clear Polycarbonate	S3083			S3084			

Covers – One Required per Gang

Material	S3825	S3625	S3826	S2425	S2625	S2825	S3813
Brass	S3825	S3625	S3826	S2425	S2625	S2825	S3813
Aluminum	SA3825	SA3625	SA3826	SA2425	SA2625	-	SA3813
Dimensions	4.15" x 2.99"						
							
	Duplex Flap	Duplex Screw	Style Line® Decorator Opening	2 1/8" x 3/4" Combination	2 1/8" x 1" Combination	2 1/8" Single Receptacle	Blank

Dimensions in Inches (mm)