











**Dimensions Inches (mm)**








Style	Cast Iron						
	1-Gang Deep	2-Gang Deep	3-Gang Deep	1-Gang Shallow	2-Gang Shallow	3-Gang Shallow	
							
Collar Material: Brass Aluminum	<b>B2436*</b> <b>BA2436*</b>	<b>B243641*</b> <b>BA243641*</b>	<b>B4233</b> <b>B423341</b> <b>BA4233</b> <b>BA423341</b>	<b>B4333</b> <b>B433361</b> <b>BA4333</b> <b>BA433361</b>	<b>B2437*</b> -	<b>B2414*</b> <b>BA2414*</b>	<b>B4214</b> <b>B4314</b> <b>BA4214</b> -
Min. Depth of Pour	3.75" (95.3)	3.75" (95.3)	3.75" (95.3)	3.00" (76.2)	2.00" (50.8)	2.00" (50.8)	2.00" (50.8)
Adjustability	Fully	Fully	Fully	Fully	Semi	Semi	Semi
Before Pour External Height Adjustment	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)
After Pour Internal Height Adjustment	.38" (9.5)	.63" (15.9)	.63" (15.9)	.38" (9.5)	-	-	-
Cubic Inch (cm <sup>3</sup> ) Capacity Per Gang	33.0 cu. in. (540.7 cm <sup>3</sup> )	36.5 cu. in. (598.1 cm <sup>3</sup> )	34.8 cu. in. (570.3 cm <sup>3</sup> )	30.0 cu. in. (491.7 cm <sup>3</sup> )	16.0 cu. in. (262.2 cm <sup>3</sup> )	16.0 cu. in. (262.2 cm <sup>3</sup> )	16.0 cu. in. (262.2 cm <sup>3</sup> )
Dimensions – A	3.20" (81.3)	3.38" (85.9)	3.38" (85.9)	2.90" (73.7)	2.00" (50.8)	2.00" (50.8)	2.00" (50.8)
Dimensions – B	4.69" (119.1)	4.84" (122.9)	4.90" (122.5)	4.69" (119.1)	5.46" (138.7)	5.46" (138.7)	5.46" (138.7)
Dimensions – C	4.69" (119.1)	8.06" (204.7)	11.41" (289.8)	4.69" (119.1)	4.19" (106.4)	7.49" (190.2)	10.7" (271.8)
Dimensions – D	4.36" (110.7)	4.36" (110.7)	4.36" (110.7)	4.36" (110.8)	4.38" (111.3)	4.38" (111.3)	4.38" (111.3)
Dimensions – E	3.19" (81.0)	6.42" (163.1)	9.64" (244.9)	3.20" (81.3)	3.19" (81.0)	6.38" (162.1)	9.56" (242.8)
Threaded Access Holes	(4) ¾" (4) 1"	(6) ¾" (4) 1" & (2) ¾"	(8) ¾" (6) 1" & (2) ¾"	(4) ¾"	(2) ¾"	(4) ¾"	(6) ¾"
Concrete Cover Included	✓	✓	✓	✓	✓	✓	✓
Closure Plugs Included	✓	✓	✓	✓	✓	✓	✓
Removable LV Barrier	-	✓	✓	-	-	-	-

Note: UL File Number E92074.  
 CSA File Number LR18416.  
 \*Suitable for single service applications only.

**Carpet Flanges**

Tapered Flange			
Number of Gangs	1-Gang	2-Gang	3-Gang
Dimensions	6.00" x 4.85"	6.00" x 8.13"	6.00" x 11.34"
Brass	<b>SB3083</b>	<b>SB3084</b>	<b>SB3085</b>
Aluminum	<b>SA3083</b>	<b>SA3084</b>	<b>SA3085</b>
Clear Polycarbonate	<b>S3083</b>	<b>S3084</b>	<b>S3085</b>
			

**Covers – One Required per Gang**

Brass	<b>S3825</b>	<b>S3625</b>	<b>S3826</b>	<b>S2425</b>	<b>S2625</b>	<b>S2825</b>	<b>S3813</b>
Aluminum	<b>SA3825</b>	<b>SA3625</b>	<b>SA3826</b>	<b>SA2425</b>	<b>SA2625</b>	-	<b>SA3813</b>
Dimensions	4.15" x 2.99"						
							
	Duplex Flap	Duplex Screw	Style Line® Decorator Opening	2 1/8" x 3/4" Combination	2 1/8" x 1" Combination	2 1/8" Single Receptacle	Blank

Dimensions in Inches (mm)