

4-conductor ground terminal block; suitable for Ex e II applications

Item No.: 2004-1407



4-conductor ground terminal block; suitable for Ex e II applications

Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	2004-1407
GTIN / EAN	4017332071833
Content	1
Order amount	50
Customer item number	

Notes



Technical data


Miscellaneous

Total number of connection points	4
Total number of potentials	1
Color	green-yellow
Connection technology (1)	Push-in CAGE CLAMP®
Nominal cross section 1	4 mm ²
Solid sizes 1	0.5 ... 6 mm ² / 20 ... 10 AWG
solid, directly pluggable 1	1 ... 6 mm ² / 14 ... 10 AWG
Fine-stranded wires 1	0.5 ... 6 mm ² / 20 ... 10 AWG
min. fine-stranded with insulated ferrule, push-in terminati	0.75 mm ² / 18 AWG
Strip length 1	11 ... 13 mm / 0.43 ... 0.51 in

Technical data	
<i>Type of wiring</i>	<i>Front-entry wiring</i>
<i>Design</i>	<i>horizontal</i>
<i>Marking level</i>	<i>Center/Side marking</i>
<i>Insulating material</i>	<i>Polyamide 66 (PA 66)</i>
<i>Fire load [MJ]</i>	<i>0.174 [MJ]</i>
<i>Weight [g]</i>	<i>16.718 [g]</i>
<i>Width</i>	<i>6.2 mm / 0.244 in</i>
<i>Height from upper-edge of DIN-rail [mm]</i>	<i>32.9 [mm]</i>
<i>Height from upper-edge of DIN-rail</i>	<i>32.9 mm / 1.295 in</i>
<i>Length</i>	<i>78.7 mm / 3.098 in</i>
<i>Type of mounting</i>	<i>DIN 35 rail</i>

Images & drawings





Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.