

Printview: Ferrule; sleeve for 0.25 mm<sup>2</sup> / awg 24; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90 - Item No.: 216-321

**WAGO**® online catalog / eShop

**Ferrule; sleeve for 0.25 mm<sup>2</sup> / awg 24; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90**

Item No.: 216-321



Ferrule; sleeve for 0.25 mm<sup>2</sup> / awg 24; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90

## Marking

RoHS ✓  
Compliant

## Business data

Supplier	WAGO
Item no.	216-321
GTIN / EAN	4017332277389
Content	1
Order amount	1,000
Customer item number	

## Notes

## Technical data

### Miscellaneous

Color	yellow
Strip length 1	7 mm / 0.28 in
Fire load [MJ]	0.001 [MJ]
Weight [g]	0.052 [g]
Diameter [mm]	2.5 [mm]
Diameter 1 [mm]	2 [mm]
Diameter 2 [mm]	0.8 [mm]
Length [mm]	10.5 [mm]

Printview: Ferrule; sleeve for 0.25 mm<sup>2</sup> / awg 24; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90 - Item No.: 216-321

---

**Technical data**

*Length 1 [mm]*


*6 [mm]*

Printview: Ferrule; sleeve for 0.25 mm<sup>2</sup> / awg 24; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90 - Item No.: 216-321

---

**Images & drawings**





#### Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.