

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301370149](#)
Status: **Active**
Overview: [Watertite® Wet-Location Wiring Solutions](#)
Description: Super-Safeway® Multiple Outlet Box, Standard Depth, 2-Sided, F2 (1/2") Cord Grip Body, Box only

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837

General

| | |
|-----------------------------|----------------------------------------------------------|
| Product Family | Power Distribution |
| Series | 130137 |
| Enclosure Rating | NEMA 4 |
| GFCI Reset | N/A |
| Mounting Style | Portable |
| Open Neutral Relay | N/A |
| Overview | Watertite® Wet-Location Wiring Solutions |
| Product Literature Order No | 987650-7737 |
| Product Name | Super-Safeway™ |
| Receptacle Type | N/A |
| Type | Multiple Outlet Box |
| UPC | 78678875075 |
| Woodhead | Yes |

Physical

| | |
|-----------------------|---------------------------|
| Cord Diameter | 7.92-15.88mm (.312-.625") |
| Cord Grip Body Size | F4 1" |
| Cord Length | N/A |
| Feed-Thru | No |
| Flip Lid | Yes |
| Material - Housing | Rubber |
| Number of Receptacles | 2 - Customer Supplied |
| Packaging Type | Carton |

Electrical

| | |
|-------------------------------|-------------------------------|
| Cord Type | N/A |
| Current - Maximum per Contact | Per Cust. Supplied Receptacle |
| GFCI | No |
| Ground Continuity Monitor | No |
| NEMA Configuration | N/A |
| Voltage - Maximum | Per Cust. Supplied Receptacle |

Material Info

Old Part Number 3059



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

Search Parts in this Series

[130137](#) Series