

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0457503112](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit® Plus Connector System](#)  
**Description:** Mini-Fit® Plus Crimp Terminal, 16 AWG, Bag, Copper (Cu) Alloy, Tin (Sn)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification PK-5556-003 \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	<a href="#">45750</a>
Application	Power
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with <a href="#">45750</a> series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current de-rating information.
Crimp Quality Equipment Overview	Yes
Packaging Alternative	<a href="#">Mini-Fit® Plus Connector System</a>
Product Name	<a href="#">45750-3111 (Reel)</a>
UPC	Mini-Fit® Plus 822350286046

**Physical**

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Copper-Nickel-Silicon
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.150/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.50mm
Wire Size AWG	16
Wire Size mm²	N/A

**Electrical**

Current - Maximum per Contact	13.0A
Voltage - Maximum	600V


**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-5556-003
Sales Drawing	SD-45750-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/21/2016 (20 June 2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
ELV

Green Image  
Not Relevant

**Search Parts in this Series**

[45750](#) Series

**Mates With**

[46012](#) Mini-Fit® Plus Crimp Terminal

**Use With**

[5557](#) Mini-Fit Jr.™, [30067](#) Mini-Fit® TPA, [42474](#) Mini-Fit® BMI Panel Mount, [43760](#) Mini-Fit® BMI, [44516](#) Mini-Fit® BMI Panel Mount Slide-N-Lock

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Hand Crimp Tool for 0638190900  
Male and Female  
Crimp Terminals,  
16-24 AWG Wire  
Extraction Tool 0011030044

This document was generated on 07/11/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**