

Class 2 Energy Limiting Plug-in *BP Series*

Features



- Used in AC powered chimes, door bells, security systems, decorative lighting, furnaces, humidifiers, appliances, vending machines, intercom system type applications.
- Enclosed in an attractive plug in black plastic case.
- For indoor use only.
- Input 120VAC - 20 VA units are inherently limited - no fuses or circuit breakers, 40 VA units use an internal slow blow fuse.
- Secondary - 2 recessed slot head screw terminals (on plug side).
- All models - 60 Hz.
- CSA certified (#LR 113601) and UL listed (#E 184936)



Gallery



Cat. No.	A.C. Input (Primary)	A.C. Output Secondary (RMS)		Power Rating
	V (RMS)	V	A	VA
BPD2E	120	12	1.67	20
BPD2EE	120	14	1.43	20
BPD2F	120	16	1.25	20
BPD2FF	120	18	1.11	20
BPD2G	120	24	0.83	20
BPE2E	120	12	3.33	40
BPE2EE	120	14	2.86	40
BPE2F	120	16	2.5	40
BPE2FF	120	18	2.22	40
BPE2G	120	24	1.67	40

Data subject to change without notice

