

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0190340005**
Status: **Active**
Overview: Snap Plugs and Receptacles
Description: InsulKrimp™ Snap Plug, for 18-22 AWG Wire, 22.61mm Length

Documents:

[3D Model](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E152602

General

Product Family Quick Disconnects
 Series 19034
 Crimp Quality Equipment Yes
 Insulated Partial
 MolexKits Yes
 Overview Snap Plugs and Receptacles
 Product Name InsulKrimp™
 Type Snap Plug
 UPC 800753047327

Physical

Barrel Type Closed
 Flammability 94V-0
 Gender Male
 Glow-Wire Compliant No
 Insulation PVC
 Lock to Mating Part None
 Material - Metal Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 1.158/g
 Orientation Straight
 Packaging Type Bag
 Tab Thickness N/A
 Tab Width N/A
 Wire Insulation Diameter 3.60mm max.
 Wire Size AWG 18, 20, 22

Electrical


Voltage - Maximum 600V

Material Info

Engineering Number A-269X

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-013-001
 Sales Drawing SD-19034-004



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/01/2017 (12
 January 2017)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS Green Image
 ELV Not Relevant
 RoHS Phthalates Not Contained

Search Parts in this Series

19034 Series