

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0191540004**  
**Status:** **Active**  
**Overview:** Splices  
**Description:** InsulKrimp™ Butt Splice for 18-22 AWG Wire

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)  
[Product Specification PS-19902-007-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-19902-011-001 \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Splices  
 Series 19154  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 MolexKits Yes  
 Overview Splices  
 Product Name Butt, InsulKrimp™  
 UPC 800753108714

**Physical**

Barrel Type Closed  
 Color - Resin Red  
 Flammability 94V-0  
 Insulation PVC  
 Material - Metal Copper  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Material - Resin PVC  
 Net Weight 1.094/g  
 Packaging Type Bag  
 Temperature Range - Operating -40°C to +105°C  
 Wire Insulation Diameter 3.68mm max.  
 Wire Size AWG 18, 20, 22  
 Wire Size mm² 0.25-1.50

**Electrical**

Voltage - Maximum 600V

**Solder Process Data**


Lead-freeProcess Capability N/A

**Material Info**

Engineering Number A-245X

**Reference - Drawing Numbers**

Product Specification PS-19902-007-001, PS-19902-011-001,  
 PS-19902-013-001  
 Sales Drawing SD-19154-006



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
 -ED/01/2017 (12  
 January 2017)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

19154 Series