

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0006660012](#)  
**Status:** **Active**  
**Overview:** [Pre-Crimped Leads](#)  
**Description:** Pre-Crimped Lead PicoBlade™ Female-to-PicoBlade™ Female, 152mm, 28 AWG

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	666
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	PicoBlade™ Crimp Terminals
Overview	<a href="#">Pre-Crimped Leads</a>
Product Name	PicoBlade™
UPC	800754232906

**Physical**

Cable Length	0.15m
Circuits (Loaded)	1
Color - Resin	Red
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	25.430/g
Packaging Type	Bag
Single Ended	No
Wire Size AWG	28
Wire/Cable Type	Discrete Wire

**Material Info**



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/01/2017 (12  
January 2017)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[666 Series](#)

**Mates With**

[50125 Crimp Terminal](#), [50133 Crimp Terminal](#)

**Use With**

[PicoBlade™ Housings 51021](#)