

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0006660013](#)
Status: **Active**
Overview: [Pre-Crimped Leads](#)
Description: Pre-Crimped Lead PicoBlade™ Female-to-PicoBlade™ Female, 304mm, 28 AWG

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	666
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	PicoBlade™ Crimp Terminals
Overview	Pre-Crimped Leads
Product Name	PicoBlade™
UPC	800754232913

Physical

Cable Length	0.30m
Circuits (Loaded)	1
Color - Resin	Red
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.500/g
Packaging Type	Bag
Single Ended	No
Wire Size AWG	28
Wire/Cable Type	Discrete Wire

Material Info



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[666 Series](#)

Mates With

[50125 Crimp Terminal](#), [50133 Crimp Terminal](#)

Use With

[PicoBlade™ Housings 51021](#)