

151-01631

HellermannTyton

Article Number: 151-01631

Description: Adhesive Base, 1.12" x 1.12", .18" Max Tie Width, .18" Hole, PA66HIRHSUV/Acrylic, Black, 100/pkg



Base Data	
Local Order Number	151-01631
Type	MB4A
Color	Black (BK)
Features and benefits	<ul style="list-style-type: none"> • For use with 18 through 50 pound HellermannTyton cable ties. • Extremely durable adhesive achieves high pull-off force and is unaffected by vibration. • Multiple sizes accommodate a range of cable ties. • 4-way opening allows cable ties to be installed parallel or perpendicular to wire bundles. • Predrilled holes extend mounting options and security. • Mount made of proprietary, impact-modified PA66 material for extraordinary durability, and is heat stabilized and UV resistant for extended life outdoors. • Peel and stick for quick, convenient use in extreme-duty applications.
Quantity Per	bag
Product Description	HellermannTyton offers adhesive mounts in a variety of sizes to match your cable tie size and extreme-duty application needs. The mount features 3M™ VHB™ (Very High Bond) adhesive, which actually builds strength over time and holds securely to difficult materials such as aluminum, steel, plastics and painted and powder-coated surfaces.
Short Description	Adhesive Base, 1.12" x 1.12", .18" Max Tie Width, .18" Hole, PA66HIRHSUV/Acrylic, Black, 100/pkg
Product Dimensions	
Length L (Imperial)	1.12"
Length L (Metric)	28.5mm
Fixation Method	Adhesive
Width W (Imperial)	1.12"
Width W (Metric)	28.5mm
Cable Tie Width Max. (Imperial)	0.18"
Cable Tie Width Max. (Metric)	4.6mm
Height H (Imperial)	0.22"
Height H (Metric)	5.6mm
Mounting Hole Diameter D (Imperial)	0.18"

151-01631



Product Dimensions	Mounting Hole Diameter D (Metric)	4.6 mm
	Mounting Hole Diameter D Min. (Imperial)	0.18"
	Mounting Hole Diameter D Max. (Imperial)	0.18"
	Mounting Hole Centers (Imperial)	0.8"
Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
	Material Shortcut	PA66HIRHSUV
	Adhesive	Acrylic foam
	Flammability	UL 94 V2 (excluding adhesive)
	Operating Temperature	-40°F to +176°F (-40°C to +80°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100
	Customs Number(Schedule B)	3926909987