

151-01529

Article Number: 151-01529

Description: Ratchet P-Clamp Tension Tab, PA66HIRHSUV, 100/bag



Base Data	Local Order Number	151-01529
	Type	RCTT
	Color	Black (BK)
	Features and benefits	• For pre-determined clamp pressure, a tension tab is available for use with our EVO® series hand tools.
	Quantity Per	bag
	Product Description	The Ratchet P-Clamp family offers optional accessories for different user needs. The Tension Tab provides a specified tension when clamping around the bundle when used with EVO® Series hand tools.
	Short Description	Ratchet P-Clamp Tension Tab, PA66HIRHSUV, 100/bag
Product Dimensions	Fixation Method	Others
	Variant	No Serration
Material and Specifications	Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
	Material Shortcut	PA66HIRHSUV
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100
	Customs Number(Schedule B)	3926909987

151-01529

HellermannTyton

Logistic and
Packaging

Content Unit (BMEcat)

pieces