


Film, Metallized Polypropylene, Safety, F863, 0.68 uF, 10%, 310 V, 110C, Lead Spacing = 22.5mm



Dimensions

| | |
|----|-----------------|
| L | 26.5mm +0.3mm |
| H | 18.5mm +0.1mm |
| T | 10mm +0.2mm |
| S | 22.5mm +/-0.4mm |
| LL | 30mm +5mm |
| F | 0.8mm +/-0.05mm |

Packaging Specifications

| | |
|---------------------|------|
| Packaging: | Bulk |
| Packaging Quantity: | 300 |

General Information

| | |
|-------------|--------------------------|
| Dielectric: | Metallized Polypropylene |
| Style: | Radial |
| Series: | F863 |
| Features: | Pulse |
| RoHS: | Yes |
| Lead: | Wire Leads |
| Approvals: | ENEC, UL, cUL, CQC |

Specifications

| | |
|------------------------|-----------|
| Capacitance: | 0.68 uF |
| Capacitance Tolerance: | 10% |
| Voltage AC: | 310 VAC |
| Temperature Range: | -40/+110C |
| Rated Temperature: | 110C |
| Dissipation Factor: | 0.2% 1KHz |
| Insulation Resistance: | 10 GOhms |
| Max dVdt: | 200 V |
| Safety Class: | X2 |