

8465 Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information
please call

1-800-Belden1



General Description:

18 AWG stranded (19x30) tinned copper conductors, conductors cabled, PVC insulation, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
5	18	19x30	TC - Tinned Copper

Total Number of Conductors: 5

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	.017

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.033

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	White
3	Red
4	Green
5	Brown

Overall Nominal Diameter: 0.282 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +60°C
UL Temperature Rating:	60°C (UL AWM Style 2598)
Bulk Cable Weight:	50 lbs/1000 ft.
Max. Recommended Pulling Tension:	125 lbs.
Min. Bend Radius/Minor Axis:	3 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
AWM Specification:	UL Style 2598 (300 V 60°C)
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes

ENGLISH MEASUREMENT VERSION

8465 Multi-Conductor - Audio, Control and Instrumentation Cable

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

Mil Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: UL1685 FT4 Loading

CSA Flame Test: FT4

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

26

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

6.3

Max. Operating Voltage - UL:

Voltage

300 V RMS (UL AWM Style 2598)

Max. Recommended Current:

Current

4 Amps per conductor @ 25°C

Notes (Overall)

Notes: Nominal Loop Inductance: .18 µH/ft.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8465 060U1000	1,000 FT	52.000 LB	CHROME		5 #18 PVC PVC
8465 060U500	500 FT	26.500 LB	CHROME		5 #18 PVC PVC
8465 060100	100 FT	5.700 LB	CHROME		5 #18 PVC PVC
8465 0601000	1,000 FT	53.000 LB	CHROME	C	5 #18 PVC PVC
8465 060500	500 FT	27.000 LB	CHROME	C	5 #18 PVC PVC
8465 0605000	5,000 FT	270.000 LB	CHROME		5 #18 PVC PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 08-14-2012

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).