



### Purchase

APC  
 NET9RMBLK

### Overview

Model Name	APC Black Rackmount SurgeArrest 9 Outlet 120V
Includes	Cord management rails , Plug pull protectors , Rack Mounting brackets , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Canada , Mexico , United States

### Output

Number of Outlets	9
Receptacle Style	NEMA 5-15R

### Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 5 Hz (auto sensing)
Input Connections	NEMA 5-15P
Maximum Line Current per phase	15.0 A
Cord Length	4.57 meters
Maximum Input Current	15 A

### Surge Protection and Filtering

Surge energy rating	2770 joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	90.0 dB
Peak Current Normal Mode	26 kA
Peak Current Common Mode	40.0 kA
NM Surge Response Time (ns)	0.0 ns
Let Through Voltage Rating	40

## Physical

Net Weight	2.19 kg
Maximum Height	44.0 mm
Maximum Width	483.0 mm
Maximum Depth	146.0 mm
Shipping Weight	2.77 kg
Shipping Height	70.0 mm
Shipping Width	483.0 mm
Shipping Depth	343.0 mm
Master Carton Units	6.0
Master Carton Dimensions (Length x Width x Height)	15 x 10 x 21 inches
Master Carton Weight	13.14 kg
SCC Codes	1073130424862 7
Color	Black
Units per Pallet	0.0

## Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

## Conformance

Approvals	CSA , UL 1283 , UL 1449 , UL Listed
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$25000
UL 1449 TVSS Rating	330

## Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs