

Isobar 12-Outlet Network Server Surge Protector, 1U Rack-Mount, 15-ft Cord, 3840 Joules, 5-20P, 20A

MODEL NUMBER: IBAR12-20ULTRA



Highlights

- 12 outlets (15- and 20-amp)/15 ft. cord
- 3840 joule rating
- All metal housing with LEDs
- Adjustable rackmount hardware
- \$25,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

Package Includes

- IBAR12/20ULTRA Surge Suppressor
- Warranty information
- Instruction manual

Description

Tripp Lite's IBAR12/20ULTRA offers network-grade surge and noise suppression in a versatile all-metal multi-mount cabinet with NEMA 5-20P input plug and 20 amp capacity. Detachable mounting flanges are configurable for rackmount, wallmount and under-counter installation, using only 1 rack space (1U) when installed in any 19 inch EIA standard rack. Features network grade AC surge suppression with EMI/RFI noise filtering. Outlets are arranged in exclusive isolated filter banks to limit noise interaction among connected items. Includes 12 outlets (2 front mounted 15 amp / 10 rear mounted 20 amp), 15 ft AC power cord and guarded power switch to reduce the risk of accidental shutoff. Diagnostic LEDs indicate AC present, line fault and protection status. \$25,000 ultimate lifetime Insurance (USA and Canada Only) coverage .

PLUG/OUTLETS: Input: NEMA 5-20P / Output: 2 NEMA5-15R (front) & 10 NEMA5-20R (rear)

ELECTRICAL: 120V AC, 50/60Hz, 20A (Requires NEMA 5-20R wall receptacle)

SUPPRESSION: AC: 140V RMS Clamping / 3840 joules / 60,000 amps

FORMAT: Supports 19 in. rackmount (uses 1 rack space / 1U), wallmount, under-counter and more

Features

- Versatile all-metal cabinet with detachable mounting flanges allows rackmount, wallmount, undercounter and other creative mounting options
- Uses one rack space (1U) in standard 19 inch rack ("zero U" mounting possible in many racks)
- 3840 joules/96,000 amp network grade AC surge suppression
- EMI/RFI filtering
- 12 outlets (2 front mounted 15 amp/10 rear mounted 20 amp)
- Outlets are arranged in exclusive isolated filter banks to limit noise interaction with connected items
- 15 foot AC cord with NEMA5-20P straight-in plug connection
- Diagnostic LEDs confirm AC Present (green), Line Fault (red) and Protected (green)
- Lighted power switch confirms power on/off status
- Snap-in switch guard prevents accidental turn off
- 20 amp capacity with circuit breaker



- 120V AC, 50/60Hz electrical compatibility
- \$25,000 Ultimate Lifetime Insurance (USA and Canada Only)

Specifications

OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(12) 5-15R
Output (Watts)	2400
Circuit Breaker (amps)	20
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-20P input plug
Input Plug Features	Space-saving right angle input plug
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Voltage Compatibility (VAC)	120
Maximum Surge Amps	150000
Right-Angle Plug	Yes
USER INTERFACE, ALERTS & CONTROLS	
Switches	Red illuminated power switch controls power to all outlets
Diagnostic LED Details	PROTECTION PRESENT (green), LINE FAULT (red) and LINE OK (green)
Locking Switch Cover	Transparent locking switch cover prevents accidental shutoff
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	3840
AC Suppression Response Time	NM = 0 ns. CM = <1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	140
AC Suppression Surge Current Rating	96,000 amps
AC Suppression Components Used	Metal oxide varistors, toroidal balanced chokes and VHF capacitors
Safe Thermal Fusing	Prevents unsafe conditions during extreme extended overvoltages and catastrophic occurrences
UL1449 Let Through Rating	330V



EMI / RFI Filtering	40-80 dB
Immunity	Conforms to IEE 587 / ANSI C62.41
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.25 x 20.5 x 9.25
Shipping Dimensions (hwd / cm)	5.72 x 52.07 x 23.50
Shipping Weight (lbs.)	6.3
Shipping Weight (kg)	2.86
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 4
Unit Dimensions (hwd / cm)	4.45 x 44.45 x 10.16
Unit Weight (lbs.)	6.3
Unit Weight (kg)	2.86
Material of Construction	Metal
Included Mounting Accessories	Included mounting flanges are pre-installed for 1U rackmount installation and can be re-configured to support a variety of mounting options
Housing Color	Black
Receptacle Color	Black
Color (AC Line Cord)	Black
Form Factors Supported	1U rackmount, 0U vertical rackmount, wallmount and under-counter mounting supported - detachable flanges can be re-configured to support a variety of additional mounting options
Outlets Measurement (Center to Center)	Distance between front outlets = 38.9mm; Distance between rear outlets = 40.65mm
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	Tested to UL1449 3rd Edition by ETL
cUL / CSA (Canada)	Approved for Canada by ETL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 Ultimate Lifetime Insurance
---	--

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>