



PRODUCT SPECIFICATIONS

28-12485 Twelve (12) outlet Power Strip (Black)

Technical Specifications

Maximum Input Voltage (VAC).....	125
Nominal Input Frequency (Hz).....	60
Maximum Output Power (Watts)	1875
Maximum Line Current (Amps).....	15
Power Control	
Switch	Yes
Circuit Breaker	15A
Lighted	Yes
Color	black and red
**Regulatory Compliance (needed on all models).....	ETL/ CETL & UL/CUL
Standard	UL 1363
Power cord	
Type	14AWG/3C 60°C
Colors	Black

Physical Specifications

Exterior Dimensions (mm).....	702 Length x 47.5 Width x 41.3 Depth
Enclosure Material	Aluminium alloy
Housing Colors	
Top.....	black
Bottom	black
Power Switch	black and red
Housing Exterior	dull polish
Enclosure Containment Design	Screws
Outlets	
Outlet Design	12 holes grounded
Total Number	12
Number of Transformer	NA

Special Features

Indicators	
Surge Indicator	NA
Clamping (Volts)	NA
Maximum Energy Dissipation	NA

Environmental

Operating Temperature	-15 to 40 degrees Celsius
Conditions of Operation	Indoor only

Product/Component Performance and Periodic Auditory Requirements

UL 1449 Transient Voltage Surge Suppressors, Second Edition	NA
UL 1363 Attachment Plugs and Receptacles	Yes

UL Markings Requirements

Product specification of 12 Outlets Power Strip

Manufacturing and Production-Line Test Requirements

Electrical Test			
Max Input voltage	Rated 1 minute	132Vac, no damage	
Power switch function	Power ON	NA	
Output rating		125V 15A 1875W	
Receptacle / Outlet mechanical test (Sampling)			
Withdraw force	after 10 insertion cycles	w 3 prongs plug	15 LB max
Retention force		w 2 prongs plug	3 LB min., 1 minute, displacement < 2 mm
Safety test			
Hi Pot test	1250Vac		1 minute, No breakdown
Leakage current test	L to G		0.5 mA max
	N to G		0.5 mA max
Insulation resistance	AC input to USB O/P		100 m ohm max

Product Markings

CAUTION: TO REDUCE THE RISK OF ELECTRIC SHOCK. USE ONLY INDOORS.
 RISK OF ELECTRIC SHOCK. DO NOT PLUG INTO ANOTHER RELOCATABLE POWER TAPS.
 NOT BE USED FOR PERMANENT MOUNTING. USE ONLY IN DRY LOCATION.
 USE ONLY IN DRY LOCATION.

ATTENTION: Pour réduire le d'électrocution, Pour Usage À L'Intérieur Seulement.

Risque de choc électrique. Ne pas brancher dans une autre source de courant portative.

Pas pour une installation permanente. EMPLOYER UNIQUEMENT DANS DES EMPLACEMENTS SECS.



RELOCATABLE POWER TAPS

RATING: 15A 125VAC 60Hz 1875W
 MADE IN CHINA
 CONFORMS TO UL STD. NO. 1363
 CERTIFIED TO CSA STD. C22.2 NO. 21

Revisions:

Rev	Description of change	Date MM/DD/YY	Approved By Initials
NR	Original	3/29/2016	Ding