



◆ SPECIFICATION

Model NO.	
Package	
NVR	1x NVRPA9204PRKTW
Camera	4 x IPR25HE200W
Hard Disk	Not included
Mouse	1xUSB 2.0 Mouse
Adaptor	1xDC12V4A for WIFI NVR, 4xDC12V0.5A for WIFI IP
Weight	4.6kg/SET
Camera Model	
Image Sensor	IMX323
Main processor	HI3518EV200
Resolution	1080P
Effective Pixels	1985(H)*1105(V)
TV System	PAL/NTSC
Electronic Shutter Time	Auto: PAL 1/25-1/10000Sec; NTSC 1/1-1/10000Sec
S/N Ratio	≥52dB
Scanning System	Progressive
Video Output	Network
Lens	
Focus Length	3.6mm
Focus Control	Fixed
Lens Type	Fixed
Pixels	3M Pixels
Night Vision	
Infrared LED	14μ x 20PCS
Infrared Distance	25M
IR Status	Under 10 Lux By CDS
IR Power On	CDS Auto Control
Network	
Ethernet	RJ-45 (10/100Base-T)
Protocol	TCP/IP, ICMP, HTTP, HTTPS, FTP, DHCP, DNS, DDNS, RTP, RTSP, RTCP, NTP, SMTP
ONVIF	Support ONVIF 2.4
P2P	YES, Support QR Code
WIFI	Support
Video Delay	0.3S (Within the Lan)
Main Stream	1920*1080@1-15fps(default resolution:1920*1080/frame rate:15fps/bit rate:1.7Mbps)
Sub Stream	720*480@1-15fps(default frame rate:15fps/bit rate:0.3Mbps)
IE Brower	IE8-11, Google Chrome, Firefox
Smart Phone	iPhone, iPad, Android, Android Pad
Camera Features	
Day/Night	Color/ B&W (IR-CUT)
Compression	H.264/JPEG/AVI
Image Config	Saturation/Brightness/Contrast /Sharpness, Mirror, 3D NR , White Balance, BLC, FLK(Flicker Control),Defog Mode
Motion Detection	Support
Privacy Masking	3 Rectangular Zone
WDR	NO
Recording Mode	NVR/NAS/CMS/Web
Language	Chinese Simplified, Chinese Traditional, English, Bulgarian, Polish, Farsi, German, Russian, French, Korean, Portuguese, Japanese, Turkish, Spanish, Hebrew, Italian, Nederlands
General	
Housing	Metal , IP66
Bracket	YES
IR Cut Filter	YES
Operation Temperature	-10℃ ~ +50℃ RH95% Max
Storage Temperature	-20℃ ~ +60℃ RH95% Max
Power Source	DC12V±10%, 500mA
Dimension	157(W) x 70(H) x 66(D)mm
Weight	650g

Model	
System	
Main Processor	ARM Cortex A9 Processor(HI3520D)
Operating System	Embedded LINUX
Video	
Input	9 Channel(4 channel wifi ipc), Support 1920×1080, 1280×960, 1280×720 ect...
Output	1 VGA, 1 HDMI
Alarm	
Sensor Input	NO
Output	NO
Motion Detection	9 Channel
Email Alarm	Support
Display	
VGA	Resolution: 1920×1080/1280×1024/1280×720
HDMI	Resolution: 1080P(1920×1080) 720P:(1280×720)
Display Split	9 channel/8 channel/4 Channel / 1Channel
Digital Zoom	YES
OSD	Camera title, Time, Video loss, Recording, Motion Detection
Recording	
Video Compression	H.264
Resolution	1080P(1920×1080) / 960P(1280×960) / 720P(1280×720) / D1 (704×576/704×480)
Record Rate	PAL :1080P@100fps, 960P@100fps, 720P@100fps, D1@100fps NTSC:1080P@120fps, 960P@120fps, 720P@120fps, D1@120fps
Record Mode	Manual\Timer\Motion Detection
Playback & Backup	
Local Sync Playback	1x1080P
Remote Sync Playback	YES
Search Mode	ALL, Channel, Time, Date, Motion Detection
Playback Functions	Play, Pause, Stop, Fast play
Backup Mode	USB Device/Network
Network	
Interface	1 RJ45 10M/100M Adaptive Ethernet Interface
Network Functions	HTTP, IPv4, TCP/IP, DNS,DHCP,NTP,PPPOE,FTP,SMTP
Onvif Version	Support Onvif 2.4
Web Browser	IE8-11, Google Chrome(IE Tab), Firefox(IE Tab)
CMS Software	Support Windows XP / Windows Vista / Windows 7/ Windows 8
Cloud Support(P2P)	Yes
Smart Phone	iPhone, iPad, Android, Android PAD
Hard Disk Driver	
Interface Type	1 SATA Interface
Capacity	2.5" / 3.5" SATA up to 6TB
General	
Language	Chinese, English, Polish, Czech, Russian, Thai, Hebrew, Arabic, Bulgarian, Farisa German, French, Portuguese, Turkic, Spanish, Italian, Hungarian, Romanian,Nederlands,Greek
USB Interface	2 USB 2.0 Interfaces
Power Supply	DC12V/2A
Working Environment	-10~55℃/10~90%
Dimension(W×D×H)	215*215*53mm
Weight	2.0KG (without HDD)