

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301100050](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Pro-Yellow 400W Metal Halide High Bay Light with Lamp Molded 18/3 SJTW 1.83m (6.0') Pulse Start

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E174253

General

Product Family Portable Lighting
 Series [130110](#)
 NEMA Configuration NEMA 5-15
 NEMA Rating Rain Tight
 Outlet None
 Overview [Wide-Area Lighting Products](#)
 Product Literature Order No 987650-8054
 Product Name Pro-Yellow
 Type Wide Area Lamps
 UPC 78172505741
 Woodhead Yes

Physical

Cord Length - Primary 0.91m (3.0')
 Cord Length - Secondary N/A
 Depth N/A
 Duty General
 Guard Included Yes
 Guard Type Metal Wire
 Height 463.55mm (18.250")
 Length N/A
 Material - Guard #10 Gauge Zinc-plated Steel
 Mounting Style Hook
 Net Weight 6477.293/g
 Packaging Type Carton
 Socket Construction N/A

Electrical


Bulb Type Metal Halide - Pulse Start
 Cord Type - Primary 16/3 SOOW
 Lamp Type BT37/ED-37 Type O
 Lamp Wattage - Maximum 400W
 Lumens 26000
 On/Off Switch No
 Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 8575-MH-PS

Reference - Drawing Numbers

Sales Drawing SD-130110-002



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Reviewed

ELV Not Reviewed

RoHS Phthalates Not Reviewed

Search Parts in this Series

[130110 Series](#)

This document was generated on 10/11/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION