


# 95 16 165 Cable Shears



- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Not suitable for steel wire and hard drawn copper conductors
- Precision ground, hardened blades
- Clean and smooth cut without crushing and deformation
- Easy cutting with one-hand operation
- Guard prevents operators' fingers being pinched
- Adjustable bolted joint, self-retaining screw
- High-grade special tool steel, forged, oil-hardened



<b>Article No.</b>	95 16 165
<b>EAN</b>	4003773039648
<b>Tool</b>	chrome plated
<b>Handles</b>	insulated with multi-component grips, VDE-tested
<b>Style</b>	1
<b>Insulation standard</b>	IEC 60900 DIN EN 60900
<b>Cutting capacity copper cable, multiple-stranded (diameter) Ø mm</b>	15
<b>Cutting capacity copper cable, multiple-stranded mm<sup>2</sup></b>	50
<b>AWG</b>	1/0
<b>Length mm</b>	165
<b>Net weight g</b>	262



Cut performed with a Diagonal Cutter: high effort required, inaccurate cut, considerable deforming and crushing of the cable



Cut performed with a Cable Shear: easy, clean cut without any deformation of the cable



technical change and errors excepted

