

80W LED Floodlight

pro-ELEC

RoHS
Compliant



Overview

- Suitable for Walls, Driveways, Buildings, Security & Flood Lighting
- Attached 1m 3-Core Mains Cable (Bare Cable)

Specifications

Light Source	: COB LED
Power Rating	: 80W
CCT	: 7000K
Total Light Output	: 4800lm
Life Time	: 30,000 Hours
Dimmable	: No
Energy Rating	: A-
IP Rating	: IP65
Dimensions (L x D x W)	: 395mm x 100mm x 285mm

Part Number Table

Description	Part Number
80W LED Floodlight	PEL00272

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.farnell.com
www.cpc.co.uk

pro-ELEC