

Miniature Surface-Mount Contacts

SM-205Q/BR

3/4" (19mm) Gap, Closed Loop, Side Leads, Brown

SM-205Q/W

3/4" (19mm) Gap, Closed Loop, Side Leads, White

Features:

- Miniature "flange type" surface-mount magnetic contacts perfect for sliding doors and windows where space is limited
- Screw or adhesive mount (adhesive backing tape included)
- Mounting flange breaks off for extra miniature size
- High-impact weatherproof ABS plastic case
- Contact reed switch is SPST, deactivated rhodium on gold under-plating for a longer expected life
- 3/4" (19mm) Gap
- 15" (38cm) leads extend from side of switch
- For closed loop circuits
- Mounting screws included
- Lifetime limited warranty




SM-205Q/BR shown



Specifications:

Model number	SM-205Q/BR	SM-205Q/W
Circuit type	Closed loop	
Operation gap	3/4" (19mm)	
Color	Brown	White
Terminals	15" (38cm) leads from side	
Material	Case	High-impact ABS plastic
	Contacts	Deactivated rhodium on gold under-plating
Contact rating	0.1A@100VDC (max)	
	1.0A@10VDC (max)	
	10W (max)	
Temperature	-15°~160°F (-25°~70°C)	
Switch cycles	50 Million (0.1mA@5VDC)	
Switch dimensions	1 3/8" x 3/8" x 1/4" (35x10x6mm)	
Magnet dimensions	1 3/8" x 3/8" x 1/4" (35x10x6mm)	
Magnet type	Alnico 5	

Dimensions:



SECO-LARM® U.S.A., Inc.

16842 Millikan Avenue, Irvine, CA 92606

Phone: (949) 261-2999 | (800) 662-0800 Fax: (949) 261-7326

Website: www.seco-larm.com Email: sales@seco-larm.com



Copyright 2015 © SECO-LARM U.S.A., Inc. All rights reserved. All trademarks are the property of SECO-LARM U.S.A., Inc. or their respective owners. The SECO-LARM policy is one of continual development. For that reason, SECO-LARM reserves the right to change prices and specifications without notice. SECO-LARM is not responsible for misprints.

SECO-LARM® ENFORCER® CRIMEBUSTER® CBA SLI

PiSM-205Q_150504.docx