

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISONS		DOC. NO.	SPC-F005	Effective:	12/21/98	DCP No:	860	
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
430	A	RELEASED	JWM	11/12/00	JC	11/22/00	DJC	11/27/00


Specifications

Cable: RG174/U Coaxial Cable - Black - 39.0" [1.0m]
 Tweezer Housing: Polyamide (Nylon) Thermoplastic - UL94V-0

Contact: BeCU - Gold Plated
 Banana Plug: 4mm, 9 Leaf-BeCU, Gold Plated

Body: Brass, Nickel Plated
 Wire: 0.75mm², PVC

Rating:
 Voltage: 400Vrms
 Current: 1A Max.
 Resistance: <15 milliohm Max.
 Temperature: 0°C ~ 50°C



DISCLAIMER
 ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TENMA[®]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY: Jeff McVicker	DATE: 11/12/00
	CHECKED BY: JOHN COLE	DATE: 11/22/00
	APPROVED BY: Daniel Carey	DATE: 11/27/00

DRAWING TITLE: SMD Tweezer w/4mm Banana Plugs		ELECTRONIC FILE	
SIZE: A	DWG. NO.: 76-001	16F7674.dwg	REV: A
SCALE: NTS	U.O.M.: INCHES [mm]	SHEET: 1	OF 1