



CorePro GLASS LED candles and lustres

CorePro LEDLusterND6.5-60W P45 E14827CLG

Featuring a classic heritage design, Classic filament LED lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. An very easy choice for people who are looking for the replacement for retrofit LED candles and lustres: compared to convential lamps, it provides a 90% energy saving. CorePro Glass LED candles and lustres provide excellent quality of light. By offering a lifetime of 15,000 hours, they reduce maintenance costs.

Product data

General Information	
Cap base	E14 [E14]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	20,000X
	Sphere
Light Technical	
Colour Code	827 [CCT of 2,700 K]
Luminous flux (nom.)	806 lm
Colour designation	Warm white (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	124.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz

Power (Rated) (Nom)	6.5 W
Lamp current (nom.)	50 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.55
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	P45 [P 45mm]

CorePro GLASS LED candles and lustres

Approval and Application


Energy Efficiency Class	E
Energy consumption kWh/1,000 hours	7 kWh
	387446

Product Data

Full product code	871951434756400
Order product name	CorePro LEDLusterND6.5-60W P45 E14827CLG

EAN/UPC – product	8719514347564
Order code	34756400
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929002028592
SAP net weight (piece)	0.014 kg


Dimensional drawing




Candle P45 60W 806lm 2700K E14 ND Clear

Product	D	C
CorePro LEDLusterND6.5-60W P45 E14827CLG	45 mm	80 mm


Photometric data



LEDbulb 6,5-60W E14 B35





LEDbulb 6,5-60W E14 B35



LEDLuster E14 P45 827 CL

CorePro GLASS LED candles and lustres

Lifetime



LEDbulb 6,5-60W E14 B35

LEDbulb 6,5-60W E14 B35

