TIME LED

SPECIFICATION SHEET

PRODUCT CODE: 769393

Offer character and candlelight to your home. The flame lamp produces a warm glow, making a comfy and relaxing atmosphere for the home or garden. The LED bulb flickers an omnidirectional warm orange flame to create a calming aura and is perfect for spaces that require a decorative light.

Complete with a gravity sensor with 3 settings: LED ON, Slow Dimming and Flame mode. With an estimated lifetime of 15,000 hours, a unique and dynamic lighting design, you are able to enjoy the LED flame effect without any risk.















NON-DIMMABLE



15,000 HOURS LIFESPAN



774373





2 YEARS WARRANTY

A+

AMBIENCE DECORATIVE FLAME **E27 OPAQUE WHITE LAMP**












SPECIFICATION

Product code

Product code	7/43/3
Fitting	ES Edison Screw (E27)
Bulb Shape	T65 Bulb
Wattage	5W
Equivalent wattage	10W
Lumens	75lm
Ra	29
Dimmable	No
Beam Angle	300°
Diameter	Ø65mm
Height	150mm
Lifespan	15,000 hours
Warranty	2 Years
Energy consumption	5kWh/1000h
Input Frequency	50Hz
Voltage	85-265V
Energy rating	A+
Material	Plastic
Packaging	Full Colour Box
IP Rating	IP20

OPTICAL TEST PARAMETERS

Voltage	85-265V
Current	47.5mA
Power	5W
ССТ	1300K
Ra	29
Lumens	25lm
Lumens per watt	85lm/W
Colour tolerance	<6
Power factor	0.4



85-265V



