


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	03/06/18	JLABOY



"P1"	WIRING MAP	"P2"
1	RED	1
2	WHITE	2
3	GREEN	3
4	BLACK	4
5	BLUE	5
6	YELLOW	6
7	DRAIN WIRE	7
8	PURPLE	8
9	ORANGE	9
SHELL	BRAID	SHELL

PART NUMBER	LENGTH METERS [FEET]
U3A00070-2M	2.0 [6.56]
U3A00070-3M	3.0 [9.84]

CABLE:
 UL STYLE 2725, (2) TWISTED PAIR, 26AWG WITH ALUM/POLY FOIL SHIELD AND DRAIN WIRE, (1) UNSHIELDED TWISTED PAIR, 28AWG, (2) CONDUCTORS, 22AWG, OVERALL ALUMINUM/MYLAR AND BRAIDED SHIELD, JACKET: PVC, BLUE (PANTONE 300C) (NOM DIA. .244" [6.2])

NOTES:
 1. METAL CRUSH RESISTANCE: 1500 PSI (MIN).
 2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 3. CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
 4. CABLE ASSEMBLY MUST MEET USB 3.0 REQUIREMENTS.
 5. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0%	APPROVALS	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845	
	DRAWN BY S.LI	08/16/17		CATEGORY USB
ALL OTHER DIMENSIONAL TOLERANCES: $.X = \pm .2$ [5.08] $.XX = \pm .02$ [1.51] $.XXX = \pm .005$ [1.13]	CHECKED BY B.ZHANG	08/16/17	PRODUCT DESCRIPTION CA, USB3.0 A/B MTL ARMOR 26/22AWG	
PROJECTION 	APPROVED BY S.PAN	08/16/17		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR
	SIZE A	FSCM NO. 43321	DWG. NO. U3A00070	REV. A
	SCALE: NONE		CAD FILE: U3A00070.SLDDRW	SHEET 1 OF 1