3-in-1 LED and Reset Switch M25 Module without Internal Jumper

multicomp PRO

RoHS Compliant

No.	Description	Qty
1	CR4305 Sponge with T4000 Ø31.7 x Ø25.5 x 4.5t, UL94HF-1	1
2	Grey, LG-DOW Calibre 301-30, UL94V-2	
3	Green LED, forward voltage: Typ.:2.2V, Max.: 2.6V, BRT P/N: BL-B2341-AT	
4	Red/Green LED forward voltage: Typ.:2.2V, Max.: 2.4V, Optosupply P/N: OSRG3131A-2OSRG3131A-2	
5	Amber LED, Forward Voltage: Typ. : 2.05V, Max.: 2.4V, Lite-On P/N LTL1CHKYK	
6	LED Spacer Support, Nylon 66/94 V2	
7	Tact Switch, DC 12V, 50mA	
8	2×4 Pin 2mm Pitch Wafer, Nylon 66, UL94V0	
9	FR4 PCB 32×26mm, T=1.6mm, UL94V0	
10	Iron, Nickel Plating, M3×0.5×12mm	2

Dimensions : Millimetres

Part Number Table

Description	Part Number
3-in-1 LED and Reset Switch M25 Module without Internal Jumper	MP1020G00000310

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO