



TECHSPRAY®

Technical Data Sheet

Roller Rejuvenator

1612

Maintenance cleaners clean oil and contaminants off of metal parts, printed circuit boards, barcode instruments, switch boxes, gear boxes, and engines.

Techspray has produced Blue Shower maintenance cleaners for over 30 years, making Blue Shower a staple in maintenance departments all over the world!

Contact cleaners remove oxidation, oil, and other contaminants off of contacts, metal switches, motors, relays, generators, edge connectors, buss bars, circuit breakers, scales and sensors. Contact cleaners are used in electrical maintenance and to repair faulty contacts by removing insulative contamination.

Techspray offers a variety of solvents and waterbased cleaners that allow customers to match the right products with their cleaning needs. Choosing a strong, high quality cleaner saves time and money. Grease and oil flow right off, reducing the time and materials needed to scrub off stubborn soils.



Rubber roller cleaner & rejuvenator

Citrus-based solvent designed to clean and revitalize rubber rollers and platens. Improves rubber roller grip and reduces misfeeds and jams.

- Improves roller grip
- Natural citrus-based solvent
- Non-ozone depleting

Product Packaging

1612-2SQ
 Rubber Rejuvenator
 2 oz
 24 units/case



Chemical & Physical Properties

Appearance	Clear to light yellow liquid
Odor	Strong, fruity odor
Flash Point	115°F
VOC (EPA)	500 to 600 g/L
VOC (CARB)	
Boiling Point	325°F to 332°F
Density	0.939 to 0.9693

Chemical Composition



Techspray - US office, P.O. Box 949,
 Amarillo, TX 79105-0949,
 Tel. 806-372-8523, Toll-free 800-858-4043
 Fax 806-372-8750, tsales@techspray.com



CHEMICAL NAME	CAS #
d-Limonene	5989-27-5
Chlorinated Paraffin	63449-39-8

Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America

Techspray
P.O. Box 949
Amarillo, TX 79105
800-858-4043
email: tsales@techspray.com

Europe

ITW Contamination Control BV
Saffierlaan 5
2132 VZ Hoofddorp
The Netherlands
+31 88 1307 400
email: info@itw-cc.com

Countries Outside US

Call to locate a distributor in your country

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.