

Amphenol

PLUGS AND SOCKETS

RCA SERIES



Features:


- Stylish design
- Flexible grommet cable protection
- Robust diecast shell
- Gold plated contacts
- Colour coded
- Good solderability
- Quick and easy assembly
- Panel mount utilises standard 'D' type housing

Part Number Breakdown: page 122

| PRODUCT - FIGURE | DRAWING | Dimensions in mm (inches) | DESCRIPTION | COLOUR | PART NUMBER |
|------------------|---------|--------------------------------|--|----------------|-------------|
| | | 62 [2.445"] ø13.8 [.543"] | RCA Plug, Diecast Shell, Gold plated contacts, Coloured finish, Flexible coloured grommet. | Red | ACPR-RED |
| | | | | Black | ACPR-BLK |
| | | | | Yellow | ACPR-YEL |
| | | | | White | ACPR-WHT |
| | | | | Blue | ACPR-BLU |
| | | 62 [2.445"] ø13.8 [.543"] | RCA Plug, Diecast Shell, Gold plated contacts, Satin finish, Flexible coloured grommet. | Satin / Red | ACPR-SRD |
| | | | | Satin / Black | ACPR-SBK |
| | | | | Satin / Yellow | ACPR-SYL |
| | | | | Satin / White | ACPR-SWH |
| | | | | Satin / Blue | ACPR-SBL |
| | | 54 [2.130"] ø13.8 [.543"] | RCA Jack, Diecast Shell, Gold plated contacts, Coloured finish, Flexible coloured grommet. | Red | ACJR-RED |
| | | | | Black | ACJR-BLK |
| | | | | Yellow | ACJR-YEL |
| | | | | White | ACJR-WHT |
| | | | | Blue | ACJR-BLU |
| | | 54 [2.130"] ø13.8 [.543"] | RCA Jack, Diecast Shell, Gold plated contacts, Satin finish, Flexible coloured grommet. | Satin / Red | ACJR-SRD |
| | | | | Satin / Black | ACJR-SBK |
| | | | | Satin / Yellow | ACJR-SYL |
| | | | | Satin / White | ACJR-SWH |
| | | | | Satin / Blue | ACJR-SBL |
| | | 50.5 [1.988"] ø13.8 [.543"] | RCA Plug, Shortened Diecast Shell, Gold plated contacts, Black Chrome finish, Flexible coloured grommet. | Red | ACPL-CRD |
| | | | | Black | ACPL-CBK |
| | | | | Yellow | ACPL-CYL |
| | | | | White | ACPL-CWH |
| | | | | Blue | ACPL-CBL |
| | | | | Green | ACPL-CGR |

NOTE: RCA Series comply with EU RoHS 2 Directive 2011/65/EU




| | | | | |
|---|--|--|--------|----------|
|  | | <p>RCA Jack, Diecast Shell, Gold plated contacts, Nickel finish shell, coloured insulator.</p> | Red | ACJD-RED |
| | | | Black | ACJD-BLK |
| | | | Yellow | ACJD-YEL |
| | | | White | ACJD-WHT |
| | | | Blue | ACJD-BLU |
| | | | Green | ACJD-GRN |

NOTE: RCA Series comply with EU RoHS 2 Directive 2011/65/EU

PART NUMBER BREAKDOWN

M SERIES RCA

E. G. **ACPR-RED BULK**
AC (Series Prefix), **P** (Plug), **R** (Shell type), **RED** (Shell and Grommet Colour), **Bulk** Packaged.



| | | | |
|---|-------|-----------------------------|------------------------------|
| SERIES PREFIX | AC | = | Series Prefix |
| CONTACT TYPE | J | = | RCA Female Jack |
| | P | = | RCA Male Plug |
| SHELL TYPE | R | = | Regular Shell Length |
| | L | = | Short Shell Length |
| | D | = | Chassis Jack 'D' Shell |
| SHELL AND GROMMET COLOUR | RED | = | Red, Red Grommet |
| | BLK | = | Black, Black Grommet |
| | YEL | = | Yellow, Yellow Grommet |
| | WHT | = | White, White Grommet |
| | BLU | = | Blue, Blue Grommet |
| | GRN | = | Green, Green Grommet |
| | SRD | = | Satin Nickel, Red Grommet |
| | CRD | = | Black Chrome, Red Grommet |
| | SBK | = | Satin Nickel, Black Grommet |
| | CBK | = | Black Chrome, Black Grommet |
| | SYL | = | Satin Nickel, Yellow Grommet |
| | CYL | = | Black Chrome, Yellow Grommet |
| | SWH | = | Satin Nickel, White Grommet |
| | CWH | = | Black Chrome, White Grommet |
| | SBL | = | Satin Nickel, Blue Grommet |
| | CBL | = | Black Chrome, Blue Grommet |
| SGR | = | Satin Nickel, Green Grommet | |
| CGR | = | Black Chrome, Green Grommet | |
| NOTE: Denotes colour of insulator only on shell type D, Chassis Jack 'D' Shell. Shell finish is Nickel. | | | |
| PACKAGING | Blank | = | Individual Bags |
| | BULK | = | Bulk Packed |

