

A range of high quality UK manufactured phono plugs made from machined brass with various plating options.

- Spring centre contacts for good electrical contact with large solder buckets.
- Internal cable clamp for secure cable connection.
- Spring strain relief.
- Colour coded ID rings for easy cable identification
- Attractive body styling.
- Maximum cable size 5.5mm

Rating -

Rated Current: 5A.



Rated Voltage: 50V

Insulation resistance – 100MΩ at 500 Vdc

Mechanical Properties

Centre contact	Brass, flash gold plated
Ground contact	Brass, flash gold plated
Insulation	Noryl SE1
Cable clamp	Brass, flash gold plated
Spring	Spring Steel
Cap	flash gold plated
	Brass, flash gold plated

Dimensions



Deltron Part No	Description
341-0000	FLASH GOLD PLATED
341-0100	FLASH GOLD PLATED (BLACK ID RING)
341-0200	FLASH GOLD PLATED (BLUE ID RING)
341-0500	FLASH GOLD PLATED (RED ID RING)
341-0600	FLASH GOLD PLATED (WHITE ID RING)
341-0700	FLASH GOLD PLATED (YELLOW ID RING)

Tel No. +44(0)1724 273200 Website www.dem-uk.com

PROPRIETARY AND CONFIDENTIAL
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF
 ALPHA 3 MANUFACTURING.
 ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF
 ALPHA 3 MANUFACTURING IS PROHIBITED.

UNLESS OTHERWISE SPECIFIED:
 DIMENSIONS ARE IN MILLIMETRES
 LINEAR TOLERANCE:
NO DECIMAL PLACES ±0.5mm
1 DECIMAL PLACE ±0.25mm
2 DECIMAL PLACES ±0.125mm
 ANGULAR TOLERANCE: ±1°

FINISH PROFESSIONAL PHONO
 LINE
 SOCKET
 IF IN DOUBT ASK
 DO NOT SCALE DRAWING

DEBURR AND BREAK
 SHARP EDGES

DRAWN BY
 APPROVED BY
 THIRD ANGLE PROJECTION

SPB
 WC
 SHEET 1 OF 1
 SCALE 1:1
 A4

TITLE GENERAL SPECIFICATION
 341 SERIES
 SOCKET
 DRAWING NO. 341 SERIES
 ISSUE 03
 Release



DEM Manufacturing, Deltron Emcon House
 Hargreaves Way, Sawcliffe Ind. Park,
 Scunthorpe, North Lincolnshire, DN15 8RF, UK