



DCB205
20V MAX* Premium XR
Lithium Ion Battery

DCB204
20V MAX* Premium XR
Lithium Ion Battery

DCB203
20V MAX* XR Lithium Ion Compact
Battery

DCB200
20V MAX* Lithium Ion
Battery



DCB201
20V MAX* Lithium Ion
Compact Battery

DCB120
12V MAX* Lithium Ion
Battery

DCB127
12V MAX* Lithium Ion
Battery

DCB080
8V MAX* Lithium Ion
Battery

8V MAX* 12V MAX* & 20V MAX* CHARGERS



8V MAX*
Lithium Ion Battery Charger

12V MAX* - 20V MAX*
Lithium Ion Battery Charger

12V MAX* - 20V MAX*
Lithium Ion Charger/Radio

12V MAX* - 20V MAX*
Lithium Ion Battery Charger

12V MAX* - 20V MAX*
Dual Port Charger

12V MAX* - 20V MAX* & 7.2V - 18V
Dual System, Dual Port Charger

SPECIFICATIONS	DCB095	DCB101	DCR015	DCB119	DCB102	DCB103
DCB080 8V MAX*	60	X	X	X	X	X
DCB120 12V MAX*	X	30	45	45	45	45
DCB200 20V MAX*	X	60	90	90	90	90
DCB201 20V MAX*	X	30	45	45	30	30
DCB203 20V MAX*	X	35	60	60	35	35
DCB204 20V MAX*	X	70	120	120	70	70
DCB205 20V MAX*	X	70	120	120	70	70

X=Not Compatible



DCB361
36V Lithium Ion
Battery

DW0242
24V XR+™ Pack Fan Cooled Extended
Run-Time Battery

DC9096
18V XRP™ Battery

DC9180
18V XRP™ Lithium Ion
Battery

DC9091
14.4V XRP™ Battery

DC9071
12V XRP™ Battery

DW9061
9.6V Extended
Run-Time Battery

DW9057
7.2V Compact
Battery

CHARGERS



1-Hour Fan
Cooled Charger

1-Hour Fan Cooled
Vehicle Charger

1-Hour
Charger

NiCd/NiMH/Li-Ion
1-Hour Charger

1-Hour
Vehicle Charger

Dual Port
1-Hour Charger

Worksite
Charger/Radio

12V MAX* - 20V MAX*
& 7.2V - 18V Dual System,
Dual Port Charger

SPECIFICATIONS	DW0246	DW0249	DC9000	DC9310	DC9319	DC9320	DC012	DCB103
DCB361 36V	X	X	60	X	X	X	X	X
DW0242 24V	60	60	X	X	X	X	X	X
DC9096 18V	X	X	X	60	60	60	60	60
DC9180 18V	X	X	X	60	60	60	60	60
DC9091 14.4V	X	X	X	60	60	60	60	60
DC9071 12V	X	X	X	60	60	60	60	60
DW9061 9.6V	X	X	X	45	45	45	45	45
DW9057 7.2V	X	X	X	30	30	30	30	30

X=Not Compatible