


ITEM	PART#	DESCRIPTION	QTY	UOM
A,B	469920410	MiniFitJr Rcpt DR V2 GW 4Ckt	2	PC
C	39000077	MiniFit Term Crp Fem Chn Bs Tin 16awg	8	PC
D	--	WHITE PART ID LABEL	1	PC

FROM	TO	DESCRIPTION	COLOUR
A1	B4	1X16AWG DISC BK	BLACK
A2	B3	1X16AWG DISC BK	BLACK
A3	B2	1X16AWG DISC BK	BLACK
A4	B1	1X16AWG DISC BK	BLACK



PART NUMBER	TITLE	L1	L2(REF)
2240941040	Mini-Fit Versa R-R 4ckt 50mm disc Sn	50±5	20
2240941041	Mini-Fit Versa R-R 4ckt 100mm disc Sn	100±5	25
2240941042	Mini-Fit Versa R-R 4ckt 150mm disc Sn	150±5	25
2240941043	Mini-Fit Versa R-R 4ckt 300mm disc Sn	300±5	25
2240941044	Mini-Fit Versa R-R 4ckt 600mm disc Sn	600±5	25

MOLEX P/N  
MOLEX  
BATCH WK/YR

DETAIL A

NOTES

1. CABLE ASSEMBLY TO BE TESTED 100% FOR CONTINUITY AND POLARITY.
2. CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
3. LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
4. LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		<p>SEE TABLE</p> <p>PRODUCT CUSTOMER DRAWING</p>		
$\frac{F}{A} = 0$	DIMENSION UNITS: mm	SCALE: NTS	CURRENT REV DESC:			
$\frac{F}{E} = 0$	GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 736238			
$\frac{F}{P} = 0$	ANGULAR TOL ± °		DRWN: THANUB 2023/01/16			
DIVISIONAL SYMBOLS		4 PLACES ±	CHK'D: SKUMAR07 2023/02/06		DOCUMENT NUMBER: 2240941040	
		3 PLACES ±	APPR: SKUMAR07 2023/02/06		DOC TYPE: PSD	
		2 PLACES ±	INITIAL REVISION:		DOC PART: 000	
		1 PLACE ±	DRWN: THANUB 2023/01/16		REVISION: A	
		0 PLACES ±	APPR: SKUMAR07 2023/02/06			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING: A4-SIZE	SERIES: 224094	MATERIAL NUMBER: SEE TABLE	
					CUSTOMER: GENERAL MARKET	
					SHEET NUMBER: 1 OF 1	

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2023/15/01	A	INITIAL RELEASE	THANUB

DOCUMENT STATUS	P1	RELEASE DATE	2023/02/06	07:28:10
-----------------	----	--------------	------------	----------