


Crimp Attachment for Flexible Cable and Direct Solder for Semi-Rigid Cable

Straight Crimp Bulkhead Jack - Miniature Cable


| P.N. | Cable Group | Plt. | Ins. | Imp. | Crimp Tool |
|--------------------------|-------------|--------|--------|------|------------|
| MCX6421A1-NT30G-5-50 | C5 | Nickel | Teflon | 50 | 1 |
| MCX6421A1-3GT30G-5-50 | C5 | Gold | Teflon | 50 | 1 |
| MCX6421A1-NT30G-5A-50 | C5A | Nickel | Teflon | 50 | 2 |
| MCX6421A1-3GT30G-5A-50 | C5A | Gold | Teflon | 50 | 2 |
| MCX6421A1-NT30G-6-75 | C6 | Nickel | Teflon | 75 | 1 |
| MCX6421A1-3GT30G-6-75 | C6 | Gold | Teflon | 75 | 1 |
| MCX6421A1-NT30G-6A-75 | C6A | Nickel | Teflon | 75 | 2 |
| MCX6421A1-3GT30G-6A-75 | C6A | Gold | Teflon | 75 | 2 |
| MCX6421A1-NT30G-14-50 | 14 | Nickel | Teflon | 50 | 1 |
| MCX6421A1-N/3GT30G-14-50 | 14 | Gold | Teflon | 50 | 1 |



Assembly Instruction J - page 232

Straight Solder Bulkhead Jack - Semi-Rigid Cable

| P.N. | Cable Group | Plt. | Ins. | Imp. | Crimp Tool |
|------------------------|-------------|------|--------|------|------------|
| MCX6481A1-3GT30G-11-50 | 11 | Gold | Teflon | 50 | N/A |
| MCX6481A1-3GT30G-13-50 | 13 | Gold | Teflon | 50 | N/A |



Assembly Instruction B - page 224
Assembly Instruction C - page 225

Printed Circuit Board Connectors

Straight Jack for P.C. Board

| P.N. | Cable Group | Plt. | Ins. | Imp. | Crimp Tool |
|---------------------|-------------|--------|--------|------|------------|
| MCX6251B1-NT30G-50 | N/A | Nickel | Teflon | 50 | N/A |
| MCX6251B3-NT30G-50 | N/A | Nickel | Teflon | 50 | N/A |
| 2.92mm [.115"] LEGS | | | | | |
| MCX6251B1-3GT30G-50 | N/A | Gold | Teflon | 50 | N/A |
| MCX6251B3-3GT30G-50 | N/A | Gold | Teflon | 50 | N/A |
| 2.92mm [.115"] LEGS | | | | | |
| MCX6251B4-NT30G-50 | N/A | Nickel | Teflon | 50 | N/A |
| Surface Mount | | | | | |
| MCX6251B4-3GT30G-50 | N/A | Gold | Teflon | 50 | N/A |
| Surface Mount | | | | | |

