


ITEM	PART#	DESCRIPTION	QTY	UOM
A,B	469920610	MiniFitJr Rcpt DR V2 GW 6Ckt	2	PC
C	39000077	MiniFit Term Crp Fem Chn Bs Tin 16awg	12	PC
D	--	WHITE PART ID LABEL	1	PC

FROM	TO	DESCRIPTION	COLOUR
A1	B3	1X16AWG DISC BK	BLACK
A2	B2	1X16AWG DISC BK	BLACK
A3	B1	1X16AWG DISC BK	BLACK
A4	B6	1X16AWG DISC BK	BLACK
A5	B5	1X16AWG DISC BK	BLACK
A6	B4	1X16AWG DISC BK	BLACK



PART NUMBER	TITLE	L1	L2(REF)
2240941060	Mini-Fit Versa R-R 6ckt 50mm disc Sn	50±5	20
2240941061	Mini-Fit Versa R-R 6ckt 100mm disc Sn	100±5	25
2240941062	Mini-Fit Versa R-R 6ckt 150mm disc Sn	150±5	25
2240941063	Mini-Fit Versa R-R 6ckt 300mm disc Sn	300±5	25
2240941064	Mini-Fit Versa R-R 6ckt 600mm disc Sn	600±5	25

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

NOTES

1. CABLE ASSEMBLY TO BE TESTED 100% FOR CONTINUITY AND POLARITY.
2. CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
3. LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
4. LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.

FUNCTIONAL SYMBOLS $\frac{E}{A} = 0$ $\frac{E}{E} = 0$ $\frac{E}{P} = 0$	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		molex SEE TABLE			
	DIMENSION UNITS: mm SCALE: NTS	CURRENT REV DESC:				EC NO: 736238 DRWN: THANUB 2023/01/16 CHK'D: SKUMAR07 2023/02/06 APPR: SKUMAR07 2023/02/06
	GENERAL TOLERANCES (UNLESS SPECIFIED)		INITIAL REVISION:		DOCUMENT NUMBER: 2240941060	
	ANGULAR TOL ± °		DRWN: THANUB 2023/01/16 APPR: SKUMAR07 2023/02/06		DOC TYPE: PSD DOC PART: 000 REVISION: A	
DIVISIONAL SYMBOLS		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		
4 PLACES ±		DRAFTING		SERIES: 224094		
3 PLACES ±		MATERIAL NUMBER: SEE TABLE		CUSTOMER: GENERAL MARKET		
2 PLACES ±		SHEET NUMBER: 1 OF 1				
1 PLACE ±						
0 PLACES ±						

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2023/15/01	A	INITIAL RELEASE	THANUB

RELEASE STATUS	P1	RELEASE DATE	2023/02/06	07:28:11
----------------	----	--------------	------------	----------