


ITEM	PART#	DESCRIPTION	QTY	UOM
A	469920410	MiniFitJr Rcpt DR V2 GW 4Ckt	1	PC
B	39000077	MiniFit Term Crp Fem Chn Bs Tin 16awg	4	PC
C	--	WHITE PART ID LABEL	1	PC

FROM	TO	DESCRIPTION	COLOUR
A1	--	1X16AWG DISC BK	BLACK
A2	--	1X16AWG DISC BK	BLACK
A3	--	1X16AWG DISC BK	BLACK
A4	--	1X16AWG DISC BK	BLACK



PART NUMBER	TITLE	L1	L2(REF)
2240951040	Mini-Fit Versa R-S 4ckt 50mm disc Sn	50±5	20
2240951041	Mini-Fit Versa R-S 4ckt 100mm disc Sn	100±5	25
2240951042	Mini-Fit Versa R-S 4ckt 150mm disc Sn	150±5	25
2240951043	Mini-Fit Versa R-S 4ckt 300mm disc Sn	300±5	25
2240951044	Mini-Fit Versa R-S 4ckt 600mm disc Sn	600±5	25

MOLEX P/N  
MOLEX  
BATCH WK/YR

DETAIL A

NOTES

- CABLE ASSEMBLY TO BE TESTED 100% FOR CONTINUITY AND POLARITY.
- CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
- LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
- LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.
- TINNING SHOULD BE DONE WITH LEAD FREE SOLDER BAR ONLY.
- FREE ENDS MUST BE STRIPPED, TWISTED & TINNED. THE LENGTH OF TINNING IS 5±1 MM. TINNING DIA MUST BE 1.8 MM MAX.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2023/15/01	A	INITIAL RELEASE	THANUB

DOCUMENT STATUS	P1	RELEASE DATE	2023/02/06	07:28:12
-----------------	----	--------------	------------	----------

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
$\frac{F}{A} = 0$ $\frac{F}{E} = 0$ $\frac{F}{P} = 0$	DIMENSION UNITS	SCALE	CURRENT REV DESC:					
	mm	NTS	EC NO: 736238 DRWN: THANUB 2023/01/16 CHK'D: SKUMAR07 2023/02/06 APPR: SKUMAR07 2023/02/06 INITIAL REVISION: DRWN: THANUB 2023/01/16 APPR: SKUMAR07 2023/02/06					
	GENERAL TOLERANCES (UNLESS SPECIFIED)							
	ANGULAR TOL	± °						
4 PLACES	±							
DIVISIONAL SYMBOLS	3 PLACES	±	DOCUMENT NUMBER					
	2 PLACES	±	2240951040					
	1 PLACE	±	DOC TYPE					
	0 PLACES	±	PSD					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	REVISION	SHEET NUMBER
			A4-SIZE	224095	SEE TABLE	GENERAL MARKET	000	1 OF 1



SEE TABLE

PRODUCT CUSTOMER DRAWING