

WDD 81V

Farnell Item Numbers: 3224703 & 3061401



Nozzles: see page 123
Spare parts: see www.weller.eu

Order No.	Model	Description
-----------	-------	-------------

005 32 566 99	WDD 81V	
---------------	---------	--

- Desoldering station digital 95 W, 230 V, compressed air or inert gas operated**
- 1 channel
 - Digitally controlled electronic for soldering or desoldering tools up to 80W
 - Compressed air converter provides vacuum for the desoldering iron
 - Inlet pressure 500–600 KPA (58–87 psi) oil-free, dry compressed air or inert gas
 - Temperature range 50°C–450°C
 - Calibration box WCB 2 (see page 174) may be connected for CALIBRATION, LOCK OUT or OFFSET function
 - Protection class 1
 - Antistatic housing
 - Equipotential bonding (normal state hard grounded)
 - Automatic tool recognition
 - Dimensions: 166 x 115 x 101 mm (L x W x H)
 - **For use with external compressed air**

consists of:

005 32 586 99	PUD 81V
005 13 190 99	DSX 80
005 15 030 99	AK 20
005 13 142 00	DX 112
005 13 143 00	DX 113
005 13 500 99	

Power unit 230 V
Desoldering iron 80 W, 24 V with nozzle DX 113HM
Safety rest
Nozzle
Nozzle
Cleaning set

WDD 161V

Farnell Item Numbers: 4122756 & 7634389



Soldering Tips: see page 87 / 88
Nozzles: see page 123
Spare parts: see www.weller.eu

Order No.	Model	Description
-----------	-------	-------------

005 32 806 99	WDD 161V	
---------------	----------	--

- Desoldering station digital 165 W, 230 V, compressed air or inert gas operated**
- 2 channels
 - Digitally controlled electronic for soldering or desoldering tools up to 150W
 - Compressed air converter provides vacuum for the desoldering iron
 - Inlet pressure 500–600 KPA (58–87 psi) oil-free, dry compressed air or inert gas
 - Temperature range 50°C–450°C (550°C with WSP 150)
 - Calibration box WCB 2 (see page 174) may be connected for CALIBRATION, LOCK OUT or OFFSET function
 - Protection class 1
 - Antistatic housing
 - Equipotential bonding (normal state hard grounded)
 - Automatic tool recognition
 - Dimensions: 166 x 115 x 101 mm (L x W x H)
 - **For use with external compressed air**

consists of:

005 32 886 99	PUD 161V
005 13 190 99	DSX 80
005 29 161 99	WSP 80
005 15 030 99	AK 20
005 15 140 99	WPH 80
005 13 142 00	DX 112
005 13 143 00	DX 113
005 13 500 99	

Power unit 230 V
Desoldering iron 80 W, 24 V with nozzle DX 113HM
Soldering iron 80 W, 24 V with soldering tip LT B
Safety rest
Safety rest
Nozzle
Nozzle
Cleaning set