

Wirelessly share your 3G+ high-speed broadband connection virtually anywhere

- Create instant WiFi hotspots where DSL/cable is not available—rural locations, satellite offices, special events, and RVs
- Broadband Usage Meter measures your Internet traffic to help avoid excess usage charges
- NETGEAR Live Parental Controls keeps your Internet experience safe
- USB docking station provides optimal 3G+ reception by placing the router where the signal is strongest
- Highest WiFi and WPA security available from attacks and unwanted “guests”
- Compatible 3G+ USB modems—View a current list of compatible 3G+ USB modems and mobile service providers at www.NETGEAR.com/3G
- Convenient Universal Car Power Adapter available separately— Visit www.netgear.com/carp1000 for online availability
- Save energy with the convenient WiFi on/off and power on/off buttons
- Easily connect multiple clients to the router with a single button push with Push ‘N’ Connect



The NETGEAR Difference

MBRN3000

- ✓ Supports major mobile carriers and 3G+ USB modems
- ✓ Broadband meter with alerts
- ✓ Easy plug-and-play setup
- ✓ Live Parental Controls
- ✓ Energy saving features

STEP 1

Follow steps of the NETGEAR Smart Wizard wireless connection utility



STEP 2

Push the Push ‘N’ Connect button on your router



STEP 3

Connect securely



Create a Wi-Fi hotspot anywhere



Home and Remote Locations



Events and Conferences





Recreational Vehicles



Mobile Workforce



Connect your 3G+ Mobile Broadband Wireless-N Router to your 3G+ network

**System Requirements**

- Activated and compatible 3G+ USB modem (see current list of compatible 3G+ USB modems at <http://www.netgear.com/3G>)
- 2.4 GHz wireless adapter or Ethernet adapter and cable for each computer
- Microsoft® Windows® 7, Vista™, XP, 2000, NT, Me, 98 SP2, Mac OS X or higher, or other operating systems running a TCP/IP network
- Microsoft® Internet Explorer™ 5.0 or higher, Firefox 2.0 or higher, or Safari

Standards

- IEEE 802.11 b/g/n
- LAN ports: Four (4) 10/100 Mbps auto-sensing
- WAN port: USB 2.0

Physical Specifications

- Dimensions: 173 x 128 x 33 mm (6.81 x 5.04 x 1.30 in)
- Weight: 0.30 kg (0.65 lb)

Features

- Parental control
- Double firewall protection
- Denial-of-Service (DoS) attack prevention
- Intrusion detection and prevention (IDS)
- Wireless: WPA2-PSK, WPA-PSK, WEP
- Push 'N' Connect using Wi-Fi Protected Setup™ (WPS)
- WiFi on/off button
- VPN functionality: VPN pass-through for IPsec

Package Contents

- 3G+ Mobile Broadband Wireless-N Router (MBRN3000)
- Power adapter, localized to country of sale
- Ethernet cable
- USB docking station
- Vertical stand
- Quick install guide

Warranty

- NETGEAR 1-year Warranty

NETGEAR®

350 E. Plumeria Drive
San Jose, CA 95134-1911
1-888-NETGEAR (638-4327)
E-mail: info@NETGEAR.com
www.NETGEAR.com

© 2010 NETGEAR, Inc. NETGEAR, the NETGEAR Logo, Connect with Innovation, and Smart Wizard are trademarks and/or registered trademarks of NETGEAR, Inc. and/or subsidiaries in the United States and/or other countries. Mac and the Mac logo are trademarks of Apple Inc., registered in the U.S. and other countries. Other brand names mentioned herein are for identification purposes only and may be trademarks of their respective holder(s). Information is subject to change without notice. All rights reserved.

*Basic technical support provided for 90 days from date of purchase.

[†]MMaximum wireless signal rate derived from IEEE standard 802.11 specifications. Actual data throughput will vary. Network conditions and environmental factors, including volume of network traffic, building materials and construction, and network overhead, lower actual data throughput rate. NETGEAR makes no express or implied representations or warranties about this product's compatibility with any future standards. "N", "Wireless-N" and "802.11n" refer to compliance with IEEE 802.11n specification version 2.0 only.

¹ Works with devices supporting Wi-Fi Protected Setup® (WPS).

3G USB modem not included. View current list of compatible 3G USB modems at www.netgear.com/3G



Powered by an ENERGY STAR® qualified adapter for a better environment