

SLMSOPTB

USB to Slimline SATA CD/DVD Optical Drive Enclosure

StarTech.com 
Making hard-to-find easy!®

INFO SAFE

Installation Guide

Packaging Contents

- 1 x SLMSOPTB enclosure
- 1 x USB "Y" cable
- 1 x Package of screws
- 1 x Set of rubber feet
- 1 x installation Guide


System Requirements

- Slimline SATA CD/DVD optical drive
- USB enabled computer system with available port
- Microsoft® Windows® 2000/XP/Server 2003/Vista/Server 2008 R2/7 (32/64-bit), or Apple® Mac OS® X, or Linux®

Installation

1. Using a screw driver, remove the two small screws from the rear panel of the enclosure and remove the plastic bezel.
2. The drive tray should now slide out from the front of the enclosure.
3. Slide the slimline SATA optical drive into the drive tray from the front. Make sure the line up the slimline SATA connector on the drive to the connector at the rear of the tray.
4. Once firmly seated, use the provided screws to secure the drive to the tray using the mounting points on the side of the drive/tray.
5. Insert the assembled drive tray back into the enclosure housing.
6. Replace the plastic rear bezel and fasten using the previously removed screws.
7. Connect the provided USB cable from the enclosure to the host system. No driver installation is required.

NOTE: Only the Primary USB connector needs to be connected to the host system. If the optical drive requires more power than can be drawn from a single USB connector, then the Secondary connector may also be necessary.



Warranty Information

This product is backed by a one year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

Front View



Rear View



Specifications

Bus Interface	USB 2.0
Chipset ID	Sunplus SPIF303
Connectors	1 x USB type mini-B
Material	Aluminum (enclosure) Plastic (drive tray)
Power Adapter	None (USB powered)
Operating Temperature	0°C ~ 60°C (32°F ~ 140°F)
Storage Temperature	-20°C ~ 70°C (-4°F ~ 158°F)
Humidity	10 ~ 90% RH
Dimensions	151.0mm x 136.0mm x 20.0mm
Weight	270g
Compatible Operating Systems	Windows 2000/XP/Server 2003/ Vista/Server 2008 R2/7 (32/64-bit), Mac OS X, Linux