

<b>Acer Part No</b>	<b>LX.R4P02.113</b>
---------------------	---------------------

Product Name	AS5742Z
Model	AS5742Z-P624G50Mnkk
Description	AS5742Z-P624G50Mnkk W7HP64ASGB1 MC UMACKk_3 2*2G/500_L/6L2.2/2R/CB_bgn_1.3C_GEk_EN11
CPU Type	PMMP6200
CPU Description	Intel® Pentium® processor P6200
LCD Type	NLED15.6WXGAG
LCD Description	15.6" HD Acer CineCrystal™ LED LCD
Graphics Type	UMA
Graphics Description	UMA
VRAM Type	N
VRAM Description	No External Video Memory
Memory 1 Type	SO2GBIII10
Memory 1 Description	2 GB DDR3 Memory
Memory 2 type	SO2GBIII10
Memory 2 Description	2 GB DDR3 Memory
Memory 3 Type	N
Memory 3 Description	
Memory 4 Type	N
Memory 4 Description	
HDD 1 Type	N500GB5.4KS
HDD 1 Description	500 GB HDD
HDD 2 Type	N
HDD 2 Description	
ODD type	NSM8XS
ODD Description	DVD-Super Multi DL drive
C/Reader Type	2-in-1 card reader
C/Reader Description	2-in-1 card reader
3G Type	N
3G Description	
WLAN Type	3rd WiFi 2x2 BGN
WLAN Description	Acer Nplify™802.11b/g/n
Re-Wireless LAN Type	3rd WiFi 2x2 BGN
Re-Wireless LAN Description	802.11b/g/n
Bluetooth Type	N
Bluetooth Description	
VOIP Phone Type	N
VOIP Phone Description	
Biometrics Type	N
Biometrics Description	
Camera Type	1.3M
Camera Description	1.3 megapixel webcam
Battery Type	6CELL2.2

Battery Description	6-cell Li-ion battery
AC Adapter Type	65W
AC Adapter Description	3-pin 65W AC adapter
Remote Controller Type	N
Remote Controller Description	
Extra Cable Type	N
Extra Cable Description	
TV Tuner Type	N
TV Tuner Description	
TV Antenna Type	N
TV Antenna Description	
Wiping Cloth	N
Accessory 1 Type	N
Accessory 1 Description	N
Accessory 2 Type	
Accessory 2 Description	
Accessory 3 Type	N
Accessory 3 Description	
Accessory 4 Type	N
Accessory 4 Description	
OS Type	W7HP64
OS Description	Windows 7® Home Premium 64-bit
OS 2 Type	N
OS 2 Description	
Softload	ENGB
User Guide	EN
Power Cable	UK
Keyboard	UK
CD	-
Extra S/W Type	McAfee
Extra S/W Description	McAfee Internet Security Suite
A Cover Type	Black IMR
A Cover Description	
B Cover Type	Mirror w/Camera
B Cover Description	
NB Chipset	HM55
SB Chipset	N
LAN	N
Modem	BCM57780
Audio Codec	ALC272X
UPC	884483829330
EAN	4712842185505