

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **39-01-3048**
Status: **Active**
Overview: Mini-Fit Jr.™
Description: 4.20mm Pitch Mini-Fit Jr.™ Receptacle Housing, Dual Row, PA Polyamide Nylon 6/6, UL 94V-0, 4 Circuits

Documents:

[3D Model](#) [Test Summary TS-5556-002 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-5556-001 \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Crimp Housings
 Series 5557
 Application Power, Wire-to-Wire
 Comments Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current derating information.. See Molex product specific Mini-Fit Jr.™
 Overview Mini-Fit Jr.™
 Product Name Mini-Fit Jr.™

Physical

Breakaway No
 Circuits (maximum) 4
 Color - Resin Natural (White)
 Flammability 94V-0
 Gender Female
 Glow-Wire Compliant No
 Keying to Mating Part None
 Lock to Mating Part Yes
 Material - Resin Nylon
 Number of Rows 2
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 4.20mm
 Pitch - Termination Interface 4.20mm
 Polarized to Mating Part Yes
 Stackable No
 Temperature Range - Operating -40°C to +105°C

Electrical

Current - Maximum per Contact 13A

Material Info

Old Part Number 5557-04R1-210
 UPC 800754943208

Reference - Drawing Numbers

Product Specification PS-5556-001
 Sales Drawing SD-5557-**R1-*
 Test Summary TS-5556-002



image - Reference only

EU RoHS

ELV and RoHS Compliant

REACH SVHC Contains SVHC: No Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

5557Series

Mates With

39012046 Panel Mount Plug, 39013049 Free Hanging Plug, 5566 Vertical Headers, 5569Right Angle Headers, 42440 PCB Headers

Use With

44476 Mini-Fit® HCS Female Crimp Terminals. 45750 Mini-Fit® Plus HCS Female Crimp Terminals. 5556 Mini-Fit® Female Crimp Terminals. 444851211 Mini-Fit® High Cycle Female Crimp Terminal

This document was generated on 06/21/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION