

COMPACT-MOBIL 70000 ELECTRONIC SERVICE CASE

The trolley case as bordcase for world-wide service



The service-case

- with high quality tools for electronics
- with telescopic handle, length up to 950 mm
- mobile on installed stable rolls



COMPACT-MOBIL ELECTRICIAN'S SERVICE CASE

The multi-purpose trolley case for the assembly and maintenance of electric devices

7200 **BERNSTEIN COMPACT-MOBIL** with tool assortment 7030, 7040 and 7050

7215 **BERNSTEIN COMPACT-MOBIL** without tools

7300 **BERNSTEIN COMPACT-MOBIL** with tool assortment 7040, 7050 and 7060

Description:

as service case 7000

This tool case is also equipped with 3 removable tool trays: No. 7030, 7040 and 7050.

The trays contain all together 32 tools.

On request the tray No. 7030 may be exchanged for No. 7060 (VDE-tools).

Outside dimensions: 500 x 400 x 200 mm

Weight without tools: approx. 7.900 kg

Weight with tools 7200: approx. 11.500 kg

Weight with tools 7300: approx. 11.600 kg

Tool set:

No. Description of individual tools

Tool tray No. 7030

- 3-133-1 **Side cutters**, 145 mm, for hard wire up to 1.25 mm Ø, for soft wire up to 2.5 mm Ø, chrome-plated, BERNSTEINIT-insulation
- 3-235-1 **Telephone pliers**, 160 mm, chrome-plated, with BERNSTEINIT-insulation
- 3-732-1 **Combination pliers**, 165 mm, chrome-plated, with BERNSTEINIT-insulation
- 4-143 **Screwdriver**, to DIN 5265, special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, black tip, 125 x 5.5 mm
- 4-144 **Screwdriver**, as above, blade 150 x 6.5 mm
- 4-145 **Screwdriver**, as above, blade 150 x 8.0 mm
- 4-256 **Cross-recess screwdriver**, as above, size 1, with black tip
- 4-257 **Cross-recess screwdriver**, as above, size 2, with black tip
- 4-344 VDE **Voltage tester**, for 220 - 250 V, blade 100 x 3.5 mm
- 5-0605 **Universal stripping tool**
- 6-105 **Socket wrench**, with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, 5.5 mm A/F
- 6-107 **Socket wrench**, as above, 7.0 mm A/F

Tool tray No. 7040

- 3-575-6 **Water pump pliers**, 240 mm, chrome-plated, with insulation
- 3-815-1 **Wire strippers**, 155 mm, chrome-plated, with BERNSTEINIT insulation
- 4-272 **Cross-recess screwdriver** Pozidriv, size 1, blade made from chrome vanadium, chrome-plated, with special square BERNSTEIN handle
- 4-273 **Cross-recess screwdriver**, Pozidriv, as above, size 2
- 5-304 **Combination cutters**, 190 mm, stainless
- 5-309 **Cable stripping shears**, 190 mm, stainless, with plastic handles
- 5-501 **Cable knife**
- 7-410 **Slicker trowel** with round shank, blade width 16 mm
- 7-535 **Spirit level**, length 220 mm, with 3 levels: horizontal, vertical and 45° angle

To complete the set we recommend for the bottom of the case:

- 5-240 **Warding file set**, 6 pieces, with wooden handles, in a wallet
- 6-810 **Set of allen hex sockets** on a ring, 8 pieces
- 7-405 **Trowel**, 50 mm
- 7-415 **Rubber beaker** for plaster
- 8-145 **ERSA soldering iron** 30 S/330 KD/30 W/230 V

No. Description of individual tools

Tool tray No. 7050

- 5-107-6 **Steel tweezers**, bent, nickel-plated, safety-insulated, 150 mm
- 5-117-6 **Steel tweezers**, straight-flat-wide, safety-insulated, 145 mm
- 5-505 **Insulation stripping tool**, with hook blade, for cable 4 - 28 mm Ø
- 7-114 **Engineer's hammer**, 200 g
- 7-202 **Firmer chisel**, blade width 16 mm
- 7-235 **Flat chisel**, 200 x 16 x 22 mm, chrome vanadium
- 7-255 **Electrician's chisel**, 200 x 8 x 10 mm, chrome vanadium
- 7-315 **Drill rasp**, bore-Ø 4 mm, length of blade 175 mm, with plastic handle
- 7-316 **Punch**, 6 mm Ø, with plastic handle
- 7-502 **Folding rule**, 2 m
- 7-616 **Pocket saw „PUK“** with adjustable wooden handle, in a wallet

Tool tray No. 7060 (VDE), alternatively to 7030

- 3-134 VDE **Side cutters**, 160 mm, for steel wire up to 1.6 mm Ø, chrome-plated, with VDE safety insulation
- 3-244 VDE **Telephone pliers**, 165 mm, snipe nose, long straight jaws, with cutting edge for hard wire, chrome-plated, with VDE safety insulation
- 3-732 VDE **Combination pliers**, 165 mm, with wire cutter, for hard wire up to 1.6 mm Ø, chrome-plated, with VDE safety insulation
- 4-344 VDE **Voltage tester**, 220 - 250 V, blade 100 x 3.5 mm
- 14-652 VDE **Screwdriver**, with VDE safety insulation, blade 100 x 3.5 mm
- 14-654 VDE **Screwdriver**, with VDE safety insulation, blade 125 x 5.5 mm
- 14-656 VDE **Screwdriver**, with VDE safety insulation, blade 150 x 6.5 mm
- 14-682 VDE **Cross-recess screwdriver**, size 1, with VDE insulation, blade length 80 mm
- 14-683 VDE **Cross-recess screwdriver**, size 2, with VDE insulation, blade length 100 mm
- 15-522 VDE **Cable stripping knife**, with blade protection, blade length 35 mm
- 16-302 VDE **Socket wrench**, with VDE insulation, 5.5 mm A/F
- 16-304 VDE **Socket wrench**, with VDE insulation, 7.0 mm A/F

COMPACT-MOBIL 7200 ELECTRICIAN'S SERVICE CASE

The trolley case as bordcase for world-wide service



alternative with
VDE-tools
7060

